

SOL Series

Industrial Solenoid Valves



- *For liquid or gas* use*
- *Full range of sizes from 3/8" to 2" (BSP)*
- *2 port, normally open (NO) and normally closed (NC) versions*
- *Pilot operated*
- *Brass body*
- *24Vdc, 110Vac and 230Vac operations available*

The SOL Series is a range of 2-way solenoid valves which are pilot-operated and are available in a choice of 110Vac, 230Vac or 24Vdc coils to suit the required voltage.

Ideal for use in a wide range of industrial and commercial applications such as autoclaves, cooling plant and equipment, watering plant, fire extinguishing systems, hygienic & sanitary applications as well as water jet machinery and many other fluid control uses.

General Features

The electro-pilot of the pilot-operated solenoid valves is not directly responsible for opening (closing) the solenoid valve. The solenoid valve presents three sequential chambers :

- inlet chamber Ci (upstream of the diaphragm)
- compensating chamber Cc (downstream of the diaphragm and upstream of the electro-pilot)
- outlet chamber Cu (downstream of the electro-pilot).

In the 2/2-way normally closed (NC) solenoid valve, Ci & Cc are communicating by means of a compensating hole when the coil is de-energised. Therefore, the diaphragm is in a condition of balanced pressure level and DN tightness is ensured by the retaining spring load from the same diaphragm.

When the coil is energised by acting on the electro-pilot, there is an immediate communication between Cc and Cu; the sudden increase in volume of the pressurised fluid over the diaphragm ($Cc + Cu > Ci$) causes a pressure drop.

The diaphragm is no longer in a condition of balanced pressure level and it swells up in the higher pressure direction thus raising up and opening the DN to let the fluid flow.

* Group 2 gases.

Mechanical Characteristics		Electrical Characteristics	
Body material	Forged brass	Electrical insulation class	I
Plunger	Magnetic stainless steel	Temperature class	H
Gaskets	NBR	Protection Class (with connector)	IP65
T _{room} Maximum	80°C	Type of service	Continuous
T _{fluid} Minimum	-20°C	Coil approval	VDE
T _{fluid} Maximum	90°C		



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email: sales@cynergy3.com

ISO9001CERTIFIED

SOL 2018


www.cynergy3.com

SOL Series

Industrial Solenoid Valves



Part No.	Operating Voltage	Solenoid Power	Operation	Size	Dimension (mm)								Pressure (bar)		Max Flow (m ³ /hr)	Operating Temp
					DN	CH.A	B	C	E	F	L	H	Min	Max		
SOL1A1	24Vdc	10 W	NO	G3/8"	11.5	24	12	32.5	42	38	57	93.5	0.1	15	1.7	-20 to +90 Deg C
SOL1B1			NC													
SOL1A3	110Vac	10.5 VA	NO													
SOL1B3			NC													
SOL1A4	230Vac	9 VA	NO													
SOL1B4			NC													
SOL2A1	24Vdc	10 W	NO	G1/2"	13.5	30	15	40	45	41	69	101	0.1	15	3.8	-20 to +90 Deg C
SOL2B1			NC													
SOL2A3	110Vac	10.5 VA	NO													
SOL2B3			NC													
SOL2A4	230Vac	9 VA	NO													
SOL2B4			NC													
SOL3A1	24Vdc	10 W	NO	G3/4"	18	36	18	46.6	54	50	74	108	0.2	15	5	-20 to +90 Deg C
SOL3B1			NC													
SOL3A3	110Vac	10.5 VA	NO													
SOL3B3			NC													
SOL3A4	230Vac	9 VA	NO													
SOL3B4			NC													
SOL4A1	24Vdc	10 W	NO	G1"	26	45	22.5	60	71	67	93	120	0.2	12	11	-20 to +90 Deg C
SOL4B1			NC													
SOL4A3	110Vac	10.5 VA	NO													
SOL4B3			NC													
SOL4A4	230Vac	9 VA	NO													
SOL4B4			NC													
SOL5A1	24Vdc	19 W	NO	G1-1/4"	32	55	27.5	73.5	87	79	111	146	0.4	12	17	-20 to +90 Deg C
SOL5B1			NC													
SOL5A3	110Vac	21 VA	NO													
SOL5B3			NC													
SOL5A4	230Vac	15 VA	NO													
SOL5B4			NC													
SOL6B1	24Vdc	19 W	NC	G1-1/2"	45	62	31	85	110	100	138	154	0.4	10	27	-20 to +90 Deg C
SOL6B3	110Vac	21 VA	NC													
SOL6A4	230Vac	9 VA	NO													
SOL6B4	230Vac	15 VA	NC	G2"	50	75	37.5	99	110	100	145	168	0.4	10	26	-20 to +90 Deg C
SOL7B1	24Vdc	19 W	NC													
SOL7B3	110Vac	21 VA	NC													
SOL7A4	230Vac	9 VA	NO													
SOL7B4		15 VA	NC													



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email:sales@cynergy3.com

ISO9001 CERTIFIED

www.cynergy3.com

© 2018 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.

Mouser Electronics

Authorized Distributor

[Click to View Pricing, Inventory, Delivery & Lifecycle Information:](#)

Sensata:

[illegible]