

Technical Data Sheet		Rosenberger
P-SMP	Adaptor	119K109-K00N5
All dimensions are in mm; tolerances according to ISO 2768 m-H Interface According to Rosenberger P-SMP Documents N/A Material and plating Connector parts Center contact Outer contact Dielectric Material CuBe CuBe PTFE Plating AuroDur®, gold plated Flash white bronze over silver(e.g. Optargen®)		
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de		Tel. : +49 8684 18-0 Email : info@rosenberger.de
		Page 1 / 2

Technical Data Sheet

Rosenberger

P-SMP

Adaptor

119K109-K00N5

Electrical data

Impedance	50 Ω
Frequency	DC to 10 GHz
Return loss	≥ 30 dB, DC to 2 GHz
	≥ 27 dB, 2 to 4 GHz
	≥ 24 dB, 4 to 6 GHz
Insertion loss	≤ 0.05 x $\sqrt{f(\text{GHz})}$ dB
Insulation resistance	≥ 5 GΩ
Center contact resistance	≤ 3.0 mΩ
Outer contact resistance	≤ 2.0 mΩ
Test voltage (at sea level)	1000 V rms
Working voltage (at sea level)	480 V rms
Power handling (at 20 °C, sea level, VSWR 1.0)	≤ 200 W @ 2.2 GHz
Intermodulation (3 rd order)	≥ 160 dBc (2 x 43 dBm)

Mechanical data

Mating cycles	
if mating part is Smooth bore, Catchers mitt	≥ 1000
if mating part is Limited detent	≥ 100
if mating part is Full detent	≥ 100
Center contact captivation	≥ 7 N
Engagement force	
- Smooth bore, Catchers mitt	≤ 10 N
- Limited detent	≤ 45 N
- Full detent	≤ 68 N
Disengagement force	
- Smooth bore, Catchers mitt	≥ 2.2 N
- Limited detent	≥ 15 N
- Full detent	≥ 25 N
Permissible angular misalignment	2.8°

Environmental data

Temperature range	-65°C to +165°C
Rapid change of temperature	IEC 60169-1, Sub-clause 16.4 (-65°C to +165°C)
Vibration	IEC 60068-2-64 random
Shock	IEC 60068-2-27 (half-sine)
High temperature endurance	IEC 60169-1, Sub-clause 18 (+165°C, 1000 hours)
RoHS	compliant

Weight

Weight	1.24 g/pce
--------	------------

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

For the installation of the electrotechnical equipment, particular electrotechnical expertise is required.



Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
S. Mühlbacher	01.02.10	Chr. Janßen	21.10.20	f00	20-1927	S. Huber-Siegl	21.10.20

Rosenberger Hochfrequenztechnik GmbH & Co. KG
P.O.Box 1260 D-84526 Tittmoning Germany
www.rosenberger.de

Tel. : +49 8684 18-0
Email : info@rosenberger.de

Page

2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[119K109-K00N5](#)