

SC420i

Loop Powered Isolator



The SC420i loop powered isolator is a 0(4)-20mA direct current isolator. The isolator derives its power from the input signal and therefore requires no external power supply.

The output of the isolator can be connected to any potential within 1kV of the input negative terminal while transients of 2.5kV can be withstood.

The isolator is typically used to enable two control and instrumentation devices, e.g. PLC and local chart recorder, with non-isolated inputs, to monitor the same transmitter output simultaneously.

Alternatively the isolator can be used to isolate signals from non-isolated transmitters or as a noise reduction device.

The device is housed in an ultra-compact DIN rail mounted enclosure, only 18mm wide.

Installation Data

Mounting	DIN Rail TS35
Orientation	Any
Connections	Screw Clamp with pressure plate
Conductor Size	0.5-4.0mm
Insulation Stripping	12mm
Weight	Approx 50g

Ordering Information

Part No.: Sc420i	4-20mA In 4-20mA Out
------------------	----------------------

- **Powered from 4-20mA input**
- **Low Voltage Drop**
- **High Accuracy**
- **1kV Isolation**
- **High Noise Immunity**
- **Low Cost Solution**

General Specifications

Recommended Operating Conditions

Input Current	0(4)-20mA
Output Current	0(4)-20mA
Output Resistance	0-600Ω
Overload Capacity	±50mA Input Current

Environmental Conditions

Storage Temperature	-40 to 100 °C
Operating Ambient	-15 to 70 °C
Relative Humidity	0-90 % RH

Other Considerations

The voltage drop across the device at 20mA input is: $V_d = 3.2 + (R_L \times 0.02)$

Technical Specifications


Parameter	Min	Typ	Max	Comments
Supply Voltage			Loop Power	
Input Current	4mA		20mA	
Full Scale Volt Drop <small>see note</small>		3.2V	3.5V	At 20mA Input
Output Linearity Error			±0.1%	
Temp Coefficient			90ppm/°C	
Load Resistance Error			-200nA/Ω	0 < R _L < 600Ω
Time Constant (10-90%)			30ms	
Operating Ambient	-15°C		70°C	
Relative Humidity	0%		90%	
Isolation Voltage	1kV			
Supply Voltage			Loop Power	
Input Current		-50mA	0-20mA	+50mA
Full Scale Volt Drop <small>see note</small>		3.2V	3.5V	At 20mA Input
Surge Voltage		2.5kV for 50μs		Transient of 10kV/μs

Notes

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. Device is protected against reverse polarity connection.

Accuracy figures based on 0-20mA input, 250Ω load resistance, and an ambient temperature of 20°C.

Add volt drop due to load: $0.02 \times R_L$ e.g. 250Ω load total volt drop = $3.5 + (0.02 \times 250) = 8.5V$



Connection Details

1. Output Channel +ve
2. Output Channel -ve
3. Input Channel +ve
4. Input Channel -ve

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sensata:](#)

[SC420i](#)