


Ultrasonic Flow Meter UF25B



- Non-invasive sensor technology
- Fully electronic, no moving parts
- Automatic viscosity and temperature compensation
- Pulse or analogue output selectable
- Low pressure drop
- LED indication of no liquid & of flow rate



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE, UK
Telephone: +44 (0)1202 897969
Email: c3w_sales@sensata.com

ISO9001 CERTIFIED

cynergy3-uf25b-v2



Made in the UK

This innovative design provides a high accuracy, non-invasive, flow measurement device at a fraction of the cost of other current non-invasive systems. The unique measurement technique automatically compensates for viscosity and temperature variations. The measurement of flow is by ultrasonic transit time in-line cell.

The flow path is designed to minimise pressure drop and, having no moving parts within, will not clog or jam. The sensor also allows contaminants to pass through without affecting its performance.

The sensor is supplied with pulse and analogue outputs, which are selectable by connection wires.

Technical Specifications

Max. flow L/min (Q4)	25
Transitional flow L/min (Q2)	0.5
Min. flow L/min (Q1)	0.2
Output selectable	Pulse Analogue

Performance

Accuracy for flow rates between Q2 and Q4	3% of reading
Accuracy for flow rates between Q1 and Q2	5% of reading
Resolution better than	0.001L/min
Flow range	0-25L/min
Response time	Better than 0.1s

Interface

Connection 8 wires (RED supply +ve, BLACK ground, Blue NPN output, Yellow - factory use only, White PNP output, Orange Voltage output, Brown Current output, Green Ground connected internally to black)

Supply	8 - 24VDC (input current <10mA @ 9VDC)
Output selectable	1000 pulses/L 0-5Vdc 4-20mA

Operation

Principle	Ultrasonic transit time in-line flow cell
Temp. range (fluid)	-10°C to 85°C
Continuous fluid sound	Maintains performance regardless of fluid type, temperature or viscosity for speed measurement fluids with sound speeds 1250 - 1750 m/s

Physical characteristics

Flow tube material	Glass filled plastic, Grivory HT1V-4FWA Black 9225 (FDA and EU approved for foodstuffs)
Flow tube internal diameter	10mm
Connection thread	3/8" BSP Parallel
Internal bore of connection	10mm
Suitable Pushfit adaptor (to fit 1/2" OD Tube)	John Guest Speedfit PI451613S
Maximum pressure	10 bar
Case material	ABS black, Polylac PA-757
Case integrity	Ultrasonically welded
Connection	8 core, PVC sheathed, 100cm long standard
Environmental protection	IP66 level of protection

Ordering Code

Series	UF 25 B 100 B	Reverse flow (B=enabled)
Flow range (25= 0 to 25L/min)		Cable length (cms)
		Output (B = selectable)

www.cynergy3.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sensata:](#)

[UF25B100](#)