



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to

Rosenberger 28K000-000, series QMA
Rosenberger is an authorised QLF® manufacturer

Documents

Assembly instruction

28E

Material and plating

Non-magnetic version

Connector parts

- Center contact
- Outer contact
- Dielectric
- Crimping ferrule

Material

- CuBe
- Spring bronze
- PTFE
- Spring bronze

Plating

- AuroDur®, gold plated
- White bronze(e.g. Optalloy®)
- Flash white bronze over silver(e.g. Optargen®)

Electrical data

Impedance	50 Ω
Frequency	DC to 18 GHz
Return loss	≥ 28 dB, DC to 6 GHz
Insertion loss	≤ 0.05 x √f(GHz) dB, DC to 6 GHz
Insulation resistance	≥ 5 x10 ³ MΩ
Center contact resistance	≤ 3 mΩ
Outer contact resistance	≤ 2.5 mΩ
Test voltage, at sea level, 50Hz	1200 V rms
Working voltage, at sea level, 50Hz	600 V rms
RF-leakage	≥ 95 dB up to 2 GHz ≥ 80 dB up to 4 GHz ≥ 70 dB up to 6 GHz
Intermodulation (3 rd order)	≤ -120 dBc @ 2 x 20 W

- Limitations are possible due to the used cable type -

Mechanical data

Mating cycles	min. 100
Center contact retention force: axial	≥ 20 N
Insulator retention force: axial	≥ 20 N
Engagement force	typ. 25 N
Disengagement force	typ. 20 N
Retention force for interface	60 N min.

Environmental data

Temperature range	-40°C to +85°C
Storage temperature	-40°C to +85°C
Thermal shock	IEC 60169-1 16.4 (-40 / +85°C)
Corrosion	IEC 60169-1 16.7 (48 hrs)
Vibration	IEC 60068-2-64 random
Damp heat, steady state	IEC 60169-1 16.3 (96 hrs)
2002/95/EC (RoHS)	compliant

Tooling

Crimp insert	11W 150 402
--------------	-------------

Suitable cables

RG 174

Packing

Standard	100 pcs in bag
Weight	2,33 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Michelmann Folke	17.01.06	H. Wurm	06.02.20	c00	20-0272	S. Hofmeister	06.02.20

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de					Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 2 / 2
--	--	--	--	--	--	--	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[28K101-102N5-NM](#)