



All dimensions are in mm; tolerances according to ISO 2768 m-H

**Interface**

According to

IEC 60169-15; EN 122110; MIL-STD-348

**Documents**

N/A

**Material and plating**

**Connector parts**

- Center conductor
- Outer conductor
- Coupling nut
- Dielectric
- Gasket
- Substrate

**Material**

- Brass
- Brass
- Brass
- PTFE
- Silicone
- Al<sub>2</sub>O<sub>3</sub>

**Plating**

- Gold, min. 1.27  $\mu\text{m}$ , over nickel
- Gold, min. 0.8  $\mu\text{m}$ , over nickel
- Gold, 0.1  $\mu\text{m}$  min.

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF\_35/09;14/6.2

# Technical Data Sheet

# Rosenberger

SMA

Termination  
Plug 1 Watt

**32S17B-1.0E3**

## Electrical data

Frequency range	DC to 18 GHz
Return loss	≥ 26.4 dB, DC to 1 GHz ≥ 19.1 dB, 1 GHz to 18 GHz
DC Resistance	50 Ω ± 2.5 Ω
Impulse Power (1μs, 1%)	100 Watts at 25°C environment temperature
Power handling	≤ 1 W at 25°C derated linearity to 0 Watts at 125°C

## Mechanical data

Mating cycles	≥ 500
Maximum torque	1.70 Nm
Recommended torque	0.90 Nm
Gauge	0.00 mm to 0.25 mm

## Environmental data

Temperature range	-55 °C to +155 °C
RoHS	compliant

## Packing

Standard	100 pcs in blister
Weight	2.3 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Kerstin Herzog	10.02.05	Markus Müller	15.09.16	b00	16-1390	Marion Striegler	15.09.16

  

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de	Tel. : +49 8684 18-0 Email : info@rosenberger.de	Page 2 / 2
--	---	---------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[32S17B-1.0E3](#)