



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to

IEC 61169-54

Contents and Documentation

This kit is delivered with

- **Standard Definitions Card**
Printed Standard Definitions that can be used on nearly all Vector Network Analyzers
- **Test Results Documentation**
- **Lanyard**
- **Hard Shell Case**
- **Protection Caps**

Material and plating

Connector parts

Center conductor
Outer conductor
Body
Dielectric
Substrate

Material

CuBe
CuBe or equiv.
Aluminum
PTFE
Al₂O₃

Plating

Gold, min. 1.27 µm, over nickel
Silver, 3-6 µm
black anodized

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09_14/6.2

Electrical data

Frequency range	DC to 12 GHz
Thru	
Return loss	≥ 36 dB, DC to 4 GHz ≥ 30 dB, 4 GHz to 6 GHz ≥ 20 dB, 6 GHz to 12 GHz
Open	
Error from nominal phase ¹	≤ 2.5°, DC to 6 GHz ≤ 3.0°, 6 GHz to 12 GHz
Short	
Error from nominal phase ²	≤ 2.5°, DC to 6 GHz ≤ 3.0°, 6 GHz to 12 GHz
Load	
Return loss	≥ 40 dB, DC to 4 GHz ≥ 35 dB, 4 GHz to 6 GHz ≥ 25 dB, 6 GHz to 12 GHz
DC-Resistance	50 Ω ± 0.5 Ω
Power handling (at 25 °C, sea level)	≤ 1.0 W, derate by 0.01 W/K

¹ The nominal phase is defined by the Offset Delay, the Offset Loss and the Fringing Capacitances

² The nominal phase is defined by the Offset Delay, the Offset Loss and the Short Inductance

Mechanical data

Mating cycles	≥ 100
Maximum torque	5 Nm
Recommended torque	2 Nm
Gauge	3.10 mm to 3.25 mm

General standard definitions

For proper operation the vector network analyzer (VNA) needs a model describing the electrical behaviour of this calibration standard. The different models, units, and terms used will depend on the VNA type and they will have to be entered into the VNA. All values are based on typical geometry and plating.

Thru

Offset Z ₀ / Impedance / Z ₀	50 Ω
Offset Delay	208.611 ps
Length (electrical) / Offset Length	62.54 mm
Offset Loss	2.50 GΩ/s
Loss	0.0453 dB/√GHz
Line Loss	0.0007 dB/mm

Open

Offset Z ₀ / Impedance / Z ₀	50 Ω
Offset Delay	66.946 ps
Length (electrical) / Offset Length	20.07 mm
Offset Loss	0.70 GΩ/s
Loss	0.0081 dB/√GHz
Fringing Capacitances	C ₀ = 8.94000 x 10 ⁻¹⁵ F / 8.94000 fF C ₁ = -4720.00 x 10 ⁻²⁷ F/Hz / -4.72000 fF /GHz C ₂ = 962.000 x 10 ⁻³⁶ F/Hz ² / 0.96200 fF /GHz ² C ₃ = -52.8000 x 10 ⁻⁴⁵ F/Hz ³ / -0.05280 fF /GHz ³

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09_14/6.2

Short

Offset Z_o / Impedance / Z_o	50 Ω
Offset Delay	66.946 ps
Length (electrical) / Offset Length	20.07 mm
Offset Loss	0.70 G Ω /s
Loss	0.0081 dB/ $\sqrt{\text{GHz}}$
Short Inductance	$L_0 = 20.400 \times 10^{-12} \text{ H} \quad / \quad 20.400 \text{ pH}$
	$L_1 = 9950.0 \times 10^{-24} \text{ H/Hz} \quad / \quad 9.9500 \text{ pH/GHz}$
	$L_2 = -2813.0 \times 10^{-33} \text{ H/Hz}^2 \quad / \quad -2.8130 \text{ pH/GHz}^2$
	$L_3 = 112.50 \times 10^{-42} \text{ H/Hz}^3 \quad / \quad 0.1125 \text{ pH/GHz}^3$

Load

Offset Z_o / Impedance / Z_o	50 Ω
Offset Delay	0.0000 ps
Length (electrical) / Offset Length	0.000 mm
Offset Loss	0.00 G Ω /s
Loss	0.0000 dB/ $\sqrt{\text{GHz}}$

Environmental data

Operating temperature range ³	+20 °C to +26 °C
Rated temperature range of use ⁴	0 °C to +50 °C
Storage temperature range	- 40 °C to +85 °C
RoHS	compliant

³ Temperature range over which these specifications are valid.

⁴ This range is underneath and above the operating temperature range, within the calibration kit is fully functional and could be used without damage

Declaration of documentation

Standard delivery for this kit includes Test Results. The documentation issued reports which quantities were tested individually, traceable to national / international standards. Model based standard definitions of the calibration standards are reported in Agilent / Keysight, Rohde & Schwarz and Anritsu compatible VNA format.

Inspection interval

Recommendation 12 months

Packing

Standard 1 pce in bag
Weight 313 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Marcel Panicke	07.06.16	Markus Müller	06.05.20	e00	19-2083	Marion Striegler	06.05.20

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 3 / 3
----------------------------------------------------------------------------------------------------------------	--	--	--	-----------------------------------------------------	--	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[64K30R-MSOTS3](#)