


**MODEL:** CUSA-TR60-06-2200-WC68 | **DESCRIPTION:** ULTRASONIC SENSOR

**FEATURES**

- aluminum can
- IP68 rated
- combination unit: receiver & transmitter
- wire leads with connector


**SPECIFICATIONS**


| parameter             | conditions/description      | min   | typ   | max   | units              |
|-----------------------|-----------------------------|-------|-------|-------|--------------------|
| type                  | transmitter/receiver        |       |       |       |                    |
| operating voltage     | at 48 kHz                   |       |       | 150   | Vp-p               |
| frequency             |                             | 46.5  | 48    | 49.5  | kHz                |
| echo sensitivity      | at 1 m                      | 120   |       |       | mV                 |
| sound pressure level  | at 10 V, 30 cm, sine wave   | 90    |       |       | dB                 |
| directivity           | horizontal angle at -6 dB   | 95    | 110   | 125   | degree             |
|                       | vertical angle at -6 dB     | 45    | 60    | 75    | degree             |
| capacitance           | at 1 kHz                    | 1,760 | 2,200 | 2,640 | pF                 |
| detectable range      |                             | 0.3   |       | 6.0   | m                  |
| response time         |                             |       |       | 1.8   | ms                 |
| impedance             |                             |       |       | 3,000 | $\Omega$           |
| dimensions            | $\varnothing 14 \times 9.0$ |       |       |       | mm                 |
| material              | aluminum                    |       |       |       |                    |
| terminal              | wire leads with connetcor   |       |       |       |                    |
| weight                |                             |       | 2.96  |       | g                  |
| operating temperature |                             | -40   |       | 80    | $^{\circ}\text{C}$ |
| storage temperature   |                             | -40   |       | 85    | $^{\circ}\text{C}$ |
| RoHS                  | yes                         |       |       |       |                    |
| IP level              | IP68                        |       |       |       |                    |

## MECHANICAL DRAWING


units: mm

wire: UL1571 30 AWG

connector: JAM P/N JB20-02HG



## BEAM PATTERNS



## PACKAGING

units: mm

Tray Size: 235 x 135 x 30 mm


Tray QTY: 50 pcs per tray

Carton Size: 280 x 285 x 240 mm


Carton QTY: 1,000 pcs per carton



50PCS/BOX  
BOX SIZE:23.5\*13.5\*3CM



10BOXES/STACK, TOTAL 500PCS  
STACK SIZE:23.5\*13.5\*31CM



1000PCS/CARTON  
CARTON SIZE:28\*28.5\*24CM

## REVISION HISTORY

| rev. | description                  | date       |
|------|------------------------------|------------|
| 1.0  | initial release              | 05/17/2022 |
| 1.01 | logo, datasheet style update | 08/05/2022 |

The revision history provided is for informational purposes only and is believed to be accurate.



CUI Devices offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI Devices reserves the right to make changes to the product at any time without notice. Information provided by CUI Devices is believed to be accurate and reliable. However, no responsibility is assumed by CUI Devices for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI Devices products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**cuidevices.com**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Devices:](#)

[CUSA-TR60-06-2200-WC68](#)