



All dimensions are in mm; tolerances according to ISO 2768 m-H

**Interface**

According to CECC 22 240

**Documents**

Panel piercing / PCB layout B 53 / B 66

**Material and plating**

**Connector parts**

	<b>Material</b>	<b>Plating</b>
Center contact	Beryllium copper	AuroDur, gold plated
Outer contact	Brass	AuroDur, gold plated
Body	Brass	AuroDur, gold plated
Dielectric	PTFE	

**Electrical data**

Impedance	75 Ω
Frequency	DC to 4 GHz
Return loss	≥ 30 dB, DC to 0.1 GHz ≥ 25 dB, 0.1 to 0.5 GHz ≥ 15 dB, 0.5 to 2 GHz
Insertion loss	≤ 0.1 dB, DC to 1 GHz
Insulation resistance	≥ 10x10 <sup>3</sup> MΩ
Center contact resistance	≤ 4 mΩ
Outer contact resistance	≤ 2 mΩ
Test voltage	1000 V rms
Working voltage	330 V rms
RF-leakage	≥ 90 dB up to 1 GHz (slide-on) ≥ 100 dB up to 1 GHz (screw version)

- Connector only, VSWR in application depends decisive on PCB layout -

**Mechanical data**

Mating cycles	≥ 500
Engaging and disengaging force	2.2 N to 12 N (screw-on, slide-on) 18 N to 50 N (quick-lock)
Center contact captivation	≥ 30 N
Torque nut for panel mounting	≤ 1 Nm
Coupling mechanism retention force	≥ 300 N (screw version, quick-lock)

**Environmental data**

Temperature range	-40°C to +85°C
Climatic class	IEC 60068-2-1 40/85/21 IEC 60068-2-2 IEC 60068-2-3
Vibration	IEC 60068-2-6 10 Hz to 2000 Hz, 100m/s <sup>2</sup>
Max. soldering temperature	IEC 61760-1, +260°C for 10 sec.
RoHS	compliant

**Tooling**

N/A

**Suitable cables**

N/A

**Weight**

Weight 6.3 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Inge Mühlauer	24/08/04	Sa. Krautenbacher	24.03.14	e00	14-0352	T. Krojer	24.03.14
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany <a href="http://www.rosenberger.de">www.rosenberger.de</a>					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: <a href="mailto:info@rosenberger.de">info@rosenberger.de</a>		Page 2 / 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[78K104-400L5](#)