




SERIES: SMI18 | DESCRIPTION: AC-DC POWER SUPPLY
FEATURES

- up to 18 W continuous power
- DoE Level VI, CoC Tier 2 efficiency
- no load power consumption < 0.075 W
- universal input voltage range
- interchangeable Ac blades for global use
- over voltage, over current, and short circuit protections
- UL/cUL, RCM, CCC, and PSE safety approvals
- certified to 60950-1 and 62368-1 standards



MODEL	input voltage	input frequency	output voltage	output current	output power	ripple and noise ¹	efficiency level ²		no load power consumption
	range (Vac)	range (Hz)	nom (Vdc)	max (A)	max (W)	max (mVp-p)	average ³ (%)	10% (%)	typ (W)
SMI18-5	90 ~ 264	47 ~ 63	5.0	3.0	15.0	100	82.2	79.0	0.07
SMI18-5.9	90 ~ 264	47 ~ 63	5.9	3.0	17.7	100	83.1	76.9	0.07
SMI18-9	90 ~ 264	47 ~ 63	9.0	2.2	19.8	100	86.5	80.7	0.07
SMI18-12	90 ~ 264	47 ~ 63	12.0	1.6	19.2	120	85.9	79.7	0.07
SMI18-15	90 ~ 264	47 ~ 63	15.0	1.3	19.5	150	88.2	81.5	0.07
SMI18-18	90 ~ 264	47 ~ 63	18.0	1.1	19.8	180	88.0	81.7	0.06
SMI18-24	90 ~ 264	47 ~ 63	24.0	0.8	19.2	240	88.7	81.8	0.07

Notes: 1. At full load, nominal AC input voltage, 25°C, 20 MHz bandwidth oscilloscope, output terminated with 0.1 μ F and 10 μ F capacitors to ground.
 2. CoC Tier 2 compliant.
 3. Average efficiency is measured at 25%, 50%, 75%, and 100% load.

PART NUMBER KEY


INPUT

parameter	conditions/description	min	typ	max	units
voltage		90	100~240	264	Vac
frequency		47	50~60	63	Hz
current				0.48	A
inrush current	at 100 Vac, full load, 25°C, cold start			50	A
	at 230 Vac, full load, 25°C, cold start			60	A
leakage current				0.25	mA
no load power consumption	at 230 Vac			0.075	W

OUTPUT

parameter	conditions/description	min	typ	max	units
regulation	5 Vdc output model		±6		%
	all other models		±5		%
hold-up time	at full load	10			ms

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	output shut down				
	5 Vdc output model			12	Vdc
	5.9 Vdc output model			12	Vdc
	9 Vdc output model			16	Vdc
	12 Vdc output model			22	Vdc
	15 Vdc output model			32	Vdc
	18 Vdc output model			32	Vdc
	24 Vdc output model			45	Vdc
over current protection	output shut down, auto recovery				
	5 Vdc output model			7.0	A
	5.9 Vdc output model			6.0	A
	9 Vdc output model			5.0	A
	12 Vdc output model			5.0	A
	15 Vdc output model			4.0	A
	18 Vdc output model			4.0	A
	24 Vdc output model			2.5	A
short circuit protection	output shut down, auto recovery				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output at 10 mA for 1 minute		3,000		Vac
isolation resistance	input to output at 500 Vdc	10			MΩ
safety approvals	certified to 60950-1: UL certified to 62368-1: UL UL/cUL, RCM, CCC, PSE, UKCA				
EMI/EMC	FCC Part 15B Class B, CE				
MTBF	as per Telcordia SR-332, 25°C	300,000			hours
RoHS	yes				

ENVIRONMENTAL


parameter	conditions/description	min	typ	max	units
operating temperature		0		40	°C
storage temperature		-20		80	°C
operating humidity	non-condensing	20		80	%
storage humidity	non-condensing	10		90	%






MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	75 x 35.8 x 65.6				mm
inlet plug	interchangeable blades (North America, Europe, UK, Australia, China)				
ac blade clip type	pinch clip				
weight	without blades		170		g

MECHANICAL DRAWING

units: mm
tolerance: ±1.0 mm



INTERCHANGEABLE BLADES					
BLADE DESIGNATOR	N	E	B	A	C
REGION	North America	Europe	UK	Australia	China
BLADE ACCESSORY	SMI-US-2	SMI-EU-2	SMI-UK-2	SMI-AU-2	SMI-CN-2
BLADE					

DC CORD

units: mm




Table 1

MODEL NO.	CABLE	CORD LENGTH
SMI18-5	UL2468, 16 AWG	1,500 mm ±30
SMI18-5.9	UL2468, 16 AWG	1,200 mm ±30
SMI18-9	UL2468, 18 AWG	1,500 mm ±30
SMI18-12	UL2468, 20 AWG	1,500 mm ±30
SMI18-15	UL2468, 22 AWG	1,500 mm ±30
SMI18-18	UL2468, 22 AWG	1,500 mm ±30
SMI18-24	UL2468, 22 AWG	1,500 mm ±30

DC PLUG TYPE PART NUMBER KEY

XXX

Plug Polarity:
P = Center Positive

N = Center Negative

Plug Code:
X = Choose a code from the options below

Plug Angle:
"blank" = Straight
R = Right Angle


Plug Polarity		Code		Dimensions (mm)			Plug Angle	
Center Pos.	Center Neg.	Option	Type	A	B	C	Straight	Right
•	•	5	Standard	5.5	2.1	9.5	•	•
•	•	6	Standard	5.5	2.5	9.5	•	•
•	•	7	Standard	3.5	1.35	9.5	•	•
•	•	8	Standard	3.8	1.35	9.5	•	•
•	•	9	Standard	3.8	1.05	9.5	•	•
•	•	10	Locking ²	5.5	2.1	9.5	•	N/A
•	•	11	Locking ²	5.5	2.5	9.5	•	N/A
•	•	12	EIAJ-1	2.35	0.7	9.5	•	•
•	•	13	EIAJ-2	4.0	1.7	9.5	•	•
•	•	14	EIAJ-3	4.75	1.7	9.5	•	•
N/A	N/A	ST	Stripped & Tinned				N/A	N/A

Note:


1. Contact CUI for additional plug options

2. Maximum insertion depth is 10mm


Standard




EIAJ



Locking



Stripped & Tinned



REVISION HISTORY

rev.	description	date
1.0	initial release	08/07/2015
1.01	added 5.9 Vdc output model	09/01/2015
1.02	updated datasheet	11/04/2015
1.03	housing width changed to 35.8 mm	01/27/2016
1.04	changed wire gauge on 5 Vdc & 5.9 Vdc models, updated datasheet	09/15/2016
1.05	added 62368-1 standard	08/31/2018
1.06	company logo updated	09/30/2020
1.07	model table updated	11/27/2020
1.08	UKCA added to the specification	05/25/2021
1.09	plug polarity symbols updated	09/16/2021
1.10	dc plugs updated	04/27/2022
1.11	ac blade clip type added	06/23/2022
1.12	datasheet updated	11/19/2024

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC
a bel group

Headquarters

15575 SW Sequoia Pkwy #100
Portland, OR 97224
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference, and
- (2) this device must accept any interference received, including interference that may cause undesired operation.

CUI offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[SMI18-24-V-P6](#) [SMI18-18-V-P5R](#) [SMI18-18-V-P6](#) [SMI18-18-K-P5](#) [SMI18-18-V-P6R](#) [SMI18-5.9-V-P5](#) [SMI18-5-K-P6R](#) [SMI18-5.9-V-P6R](#) [SMI18-12-V-P6](#) [SMI18-18-K-P6R](#) [SMI18-9-K-P6R](#) [SMI18-9-V-P5R](#) [SMI18-5-K-P5R](#) [SMI18-5.9-K-P6R](#) [SMI18-9-V-P5](#) [SMI18-24-K-P5R](#) [SMI18-9-V-P6R](#) [SMI18-9-K-P6](#) [SMI18-5.9-V-P6](#) [SMI18-5-V-P12](#) [SMI18-5-K-P6](#) [SMI18-5.9-V-P5R](#) [SMI18-15-K-P5](#) [SMI18-9-K-P5](#) [SMI18-9-V-P6](#) [SMI18-9-K-P5R](#) [SMI18-12-V-P5R](#) [SMI18-24-V-P5R](#) [SMI18-12-K-P6R](#) [SMI18-15-V-P6](#) [SMI18-24-K-P6R](#) [SMI18-5-V-P5R](#) [SMI18-15-V-P5](#) [SMI18-24-V-P6R](#) [SMI18-15-K-P5R](#) [SMI18-12-K-P5](#) [SMI18-5-V-P6R](#) [SMI18-15-V-P5R](#) [SMI18-24-K-P5](#) [SMI18-24-K-P6](#) [SMI18-5.9-K-P5R](#) [SMI18-15-V-P6R](#) [SMI18-5-K-P5](#) [SMI18-12-K-P5R](#) [SMI18-18-K-P6](#) [SMI18-15-K-P6R](#) [SMI18-12-V-P5](#) [SMI18-5-V-P6](#) [SMI18-15-K-P6](#) [SMI18-5-V-P5](#) [SMI18-5.9-K-P5](#) [SMI18-12-V-P6R](#) [SMI18-12-K-P6](#) [SMI18-24-V-P5](#) [SMI18-18-V-P5](#) [SMI18-18-K-P5R](#) [SMI18-9-V-N5R](#) [SMI18-24-V-ST](#) [SMI18-24-V-P7R](#) [SMI18-5-V-P7](#) [SMI18-24-V-N5R](#) [SMI18-5-V-P10](#) [SMI18-9-V-N5](#) [SMI18-15-K-P8](#) [SMI18-12-E-ST](#) [SMI18-9-K-ST](#) [SMI18-24-B-ST](#) [SMI18-5-N-P7](#) [SMI18-24-N-ST](#) [SMI18-24-A-ST](#) [SMI18-24-E-ST](#) [SMI18-9-V-P7](#) [SMI18-12-V-ST](#) [SMI18-15-N-P8](#) [SMI18-24-N-N5](#)