


CUI INC

a bel group


date 12/09/2024

page 1 of 5

SERIES: SWM12-N | **DESCRIPTION:** AC-DC POWER SUPPLY


FEATURES

- up to 12 W power
- certified to UL 60601 4th edition
- compact vertical or horizontal mount
- universal input (90~264 Vac)
- single regulated output from 5~24 Vdc
- over voltage and short circuit protections
- DOE Level VI efficiency*
- 2 MOPP compliant


MODEL

	output voltage (Vdc)	output current max (A)	output power max (W)	ripple and noise¹ max (mVp-p)	efficiency level
SWM12-5-N	5	2.4	12	100	VI
SWM12-6-N	6	2.0	12	120	-
SWM12-9-N	9	1.33	12	180	VI
SWM12-12-N	12	1.0	12	250	VI
SWM12-15-N	15	0.8	12	250	VI
SWM12-18-N	18	0.66	12	350	VI
SWM12-24-N	24	0.50	12	350	VI

Notes: 1. At full load, 100 ~ 240 Vac input, 20 MHz bandwidth oscilloscope, output terminated with a low ESR 47 μ F electrolytic and 0.1 μ F multilayer capacitor.
* 6V unit does not meet DoE Level VI

PART NUMBER KEY


INPUT

parameter	conditions/description	min	typ	max	units
voltage		90	100~240	264	Vac
frequency		47	50~60	63	Hz
current	at 115 Vac, full load			1.0	A
	at 230 Vac, full load			0.5	A
inrush current	at 115 Vac, full load, cold start			30	A
	at 230 Vac, full load, cold start			60	A
leakage current	at 240 Vac, 50 Hz			0.1	mA
no load power consumption	at 115/230 Vac, 60/50 Hz			0.1	W

OUTPUT

parameter	conditions/description	min	typ	max	units
line regulation			±1		%
load regulation			±5		%
start-up time	at 100 Vac, to 90% of rated output voltage			3	s
rise time	at nominal input voltage, full load, from 10% to 90% of output voltage			50	ms
hold-up time	at nominal input voltage, full load	8.3			ms

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	output shutdown, auto recovery				
over current protection	output shutdown, auto recovery			200	%
short circuit protection	output shut down, auto recovery				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output		4,000		Vac
isolation resistance	input to output at 500 Vdc for 3 seconds	50			MΩ
safety approvals	certified to 60601: UL/cUL (medical) ITE: PSE				
EMI/EMC	FCC Part 15B Class B				
MTBF	as per MIL-HDBK-217F	100,000			hours
RoHS	yes				

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature		0		40	°C
storage temperature		-20		85	°C
operating humidity	non-condensing	10		90	%
storage humidity	non-condensing	5		90	%
altitude			5,000		m


MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	horizontal models: 55 x 25 x 43 vertical models: 53 x 41 x 30				mm mm
inlet plug	North America, 2-pin				
weight	horizontal models vertical models		55 60		g g
color	black				


MECHANICAL DRAWINGS

units: mm
tolerance: ±1 mm

Horizontal Models



Vertical Models



DC CORD

units: mm




Table 1

MODEL NO.	CABLE	CORD LENGTH
SWM12-5-N	UL2468, 20 AWG	1,500 mm ±50
SWM12-6-N	UL2468, 20 AWG	1,500 mm ±50
SWM12-9-N	UL2468, 20 AWG	1,500 mm ±50
SWM12-12-N	UL2468, 22 AWG	1,500 mm ±50
SWM12-15-N	UL2468, 22 AWG	1,500 mm ±50
SWM12-18-N	UL2468, 24 AWG	1,500 mm ±50
SWM12-24-N	UL2468, 24 AWG	1,500 mm ±50

DC PLUG TYPE PART NUMBER KEY

XXX

Plug Polarity:
 P = Center Positive

 N = Center Negative


Plug Code:
 X = Choose a code from the options below

Plug Angle:
 "blank" = Straight
 R = Right Angle


Plug Polarity		Code		Dimensions (mm)			Plug Angle	
Center Pos.	Center Neg.	Option	Type	A	B	C	Straight	Right
•	•	5	Standard	5.5	2.1	9.5	•	•
•	•	6	Standard	5.5	2.5	9.5	•	•
•	•	7	Standard	3.5	1.35	9.5	•	•
•	•	8	Standard	3.8	1.35	9.5	•	•
•	•	9	Standard	3.8	1.05	9.5	•	•
•	•	12	EIAJ-1	2.35	0.7	9.5	•	•
•	•	13	EIAJ-2	4.0	1.7	9.5	•	•
•	•	14	EIAJ-3	4.75	1.7	9.5	•	•
N/A	N/A	ST	Stripped & Tinned				N/A	N/A
N/A	N/A	MUB	USB	Micro USB Type B			•	N/A
N/A	N/A	CUB	USB	USB Type C			•	N/A

Note: 1. Contact CUI for additional plug options


Standard




EIAJ



Stripped & Tinned



USB



REVISION HISTORY

rev.	description	date
1.0	initial release	06/27/2017
1.01	added PSE certification	01/24/2018
1.02	USB-C added to dc plug type number key	08/18/2020
1.03	features updated	02/18/2021
1.04	safety marks updated	04/26/2021
1.05	datasheet updated	12/09/2024

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC
a bel group

Headquarters

15575 SW Sequoia Pkwy #100
Portland, OR 97224
800.275.4899

Fax 503.612.2383

cui.com

techsupport@cui.com

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference, and
- (2) this device must accept any interference received, including interference that may cause undesired operation.

CUI offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[SWM12-12-NH-P5](#) [SWM12-5-NH-P5](#) [SWM12-24-NV-P5](#) [SWM12-12-NH-MUB](#) [SWM12-12-NH-P5R](#) [SWM12-12-NH-P6](#) [SWM12-12-NH-P6R](#) [SWM12-12-NV-MUB](#) [SWM12-12-NV-P5](#) [SWM12-12-NV-P5R](#) [SWM12-12-NV-P6](#) [SWM12-12-NV-P6R](#) [SWM12-15-NH-MUB](#) [SWM12-15-NH-P5](#) [SWM12-15-NH-P5R](#) [SWM12-15-NH-P6](#) [SWM12-15-NH-P6R](#) [SWM12-15-NV-MUB](#) [SWM12-15-NV-P5](#) [SWM12-15-NV-P5R](#) [SWM12-15-NV-P6](#) [SWM12-15-NV-P6R](#) [SWM12-18-NH-MUB](#) [SWM12-18-NH-P5](#) [SWM12-18-NH-P5R](#) [SWM12-18-NH-P6](#) [SWM12-18-NH-P6R](#) [SWM12-18-NV-MUB](#) [SWM12-18-NV-P5](#) [SWM12-18-NV-P5R](#) [SWM12-18-NV-P6](#) [SWM12-18-NV-P6R](#) [SWM12-24-NH-MUB](#) [SWM12-24-NH-P5](#) [SWM12-24-NH-P5R](#) [SWM12-24-NH-P6](#) [SWM12-24-NH-P6R](#) [SWM12-24-NV-MUB](#) [SWM12-24-NV-P5R](#) [SWM12-24-NV-P6](#) [SWM12-24-NV-P6R](#) [SWM12-5-NH-MUB](#) [SWM12-5-NH-P5R](#) [SWM12-5-NH-P6](#) [SWM12-5-NH-P6R](#) [SWM12-5-NV-MUB](#) [SWM12-5-NV-P5](#) [SWM12-5-NV-P5R](#) [SWM12-5-NV-P6](#) [SWM12-5-NV-P6R](#) [SWM12-6-NH-MUB](#) [SWM12-6-NH-P5](#) [SWM12-6-NH-P5R](#) [SWM12-6-NH-P6](#) [SWM12-6-NH-P6R](#) [SWM12-6-NV-MUB](#) [SWM12-6-NV-P5](#) [SWM12-6-NV-P5R](#) [SWM12-6-NV-P6](#) [SWM12-6-NV-P6R](#) [SWM12-9-NH-MUB](#) [SWM12-9-NH-P5](#) [SWM12-9-NH-P5R](#) [SWM12-9-NH-P6](#) [SWM12-9-NH-P6R](#) [SWM12-9-NV-MUB](#) [SWM12-9-NV-P5](#) [SWM12-9-NV-P5R](#) [SWM12-9-NV-P6](#) [SWM12-9-NV-P6R](#) [SWM12-5-NV-P7](#)