

5kV Reinforced Insulation Modules

Reinforced Insulation Isolation Modules for MAX14857/MAX14859




Product Features:

- Designed specifically for the MAX14857 and MAX14859
- Fully tested and approved by Maxim™ Integrated Products, Inc.
- UL/EN60950 and DEMKO recognized for reinforced insulation and with working voltages up to 300V
- ET Constant 15.7V-μs min.


Part Number	Turns Ratio	I/O Voltage	PRI OCL (μH Typ)	PRI DCR (ΩMax)	Isolation Voltage (Vrms)	Temp. Range
TGMR-1450V6LF	1CT:1CT	5V » 3.3V	125	0.4	5,000	-40 to +105C
TGMR-1455V6LF	1CT:1.5CT	3.3V » 3.3V	180	0.4	5,000	-40 to +105C

Notes:

1. Please contact the factory or representative for individual datasheets or additional information
2. Maxim™ is a registered trademark of Maxim Integrated Products, Inc.



Circuit Diagram



Dimensions: Inch[mm]



2880 Lakeside Drive #116
Santa Clara, CA 95054
(650) 903-3800
www.halo-electronics.com

HALO® Electronics is a leading supplier of high quality communication magnetics including signal transformers, filters, CMR chokes, PoE power transformers, DC/DC converters, and integrated Ethernet connectors. HALO's leading edge technology solutions are manufactured in ISO9001 and ISO14001 factories offering high quality products at a competitive price.

© Copyright 2016 HALO Electronics, Inc. All rights reserved.

Revised 6/2016. Download the latest version at www.halo-electronics.com/pdf/discrete-dc2dc-reinmax14857-59.pdf

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HALO Electronics:](#)

[TGMR-1455V6LF](#) [TGMR-1450V6LF](#)