


HALO Electronics offers a broad line of power transformers designed for fly-back DC/DC converters used in Power over Ethernet (PoE) applications. These industrial temperature range transformers are UL recognized and are fully compliant to IEEE802.3af requirements for isolation and power ratings. This standard series is LEAD-free and RoHS compliant. Please contact your nearest HALO representative for custom designs.




MECHANICAL DIMENSIONS

PACKAGE A



RECOMMENDED SOLDER PAD DIMENSIONS

PACKAGE B




RECOMMENDED SOLDER PAD DIMENSIONS




DIMENSIONS: Inch [mm]

TOLERANCES: 0.006 inch if not specified

SCHEMATIC A



SCHEMATIC B



Electrical Specifications @ 25 °C

Isolation Voltage (PRI – SEC): 1,500Vrms

Operating Temp: -40 to +85 °C



Part Number	Turns Ratio PRI:BIAS:SEC:DRV	DCR (mΩ max) PRI/BIAS/SEC/DRV	PRI OCL (μH ±10%)	PRI LL (μH Max)	PKG/ SCHE.	IC P/N
TGP13-S004EFD15LF	1:0.208:0.083	520/400/10	145	5	A	LTC4267
TGP13-S008EFD15LF	1: 0.500:0.167	150/400/10	33	1	A	LM5072
TGP13-S012EFD15LF	1:0.500:0.150:0.275	520/760/20/400	160	2	B	TPS23750

HALO


13W, 3.3Vout, Power Transformers (EP13) Power Over Ethernet, DC/DC Converter

ELECTRONICS, INC.

HALO Electronics offers a broad line of power transformers designed for fly-back DC/DC converters used in Power over Ethernet (PoE) applications. These industrial temperature range transformers are UL recognized and are fully compliant to IEEE802.3af requirements for isolation and power ratings. This standard series is LEAD-free and RoHS compliant. Please contact your nearest HALO representative for custom designs.




MECHANICAL DIMENSIONS




RECOMMENDED SOLDER PAD DIMENSIONS

DIMENSIONS: Inch [mm]
TOLERANCES: 0.006 inch if not specified

SCHEMATIC A



SCHEMATIC B



13W, 3.3Vout, Power Transformers (EP13)
Power Over Ethernet, DC/DC Converter

Electrical Specifications @ 25 °C
Isolation Voltage (PRI – SEC): 1,500Vrms
Operating Temp: -40 to +85 °C



Part Number	Turns Ratio PRI:AUX:SEC:DRV	DCR (mΩ max) PRI/AUX/SEC/DRV	PRI OCL (μH ±10%)	PRI LL (μH Max)	IC SCHE. P/N
TGP13-S003EP13LF	1:0.208:0.083	500/400/15	145	5	A LTC4267
TGP13-S007EP13LF	1: 0.500:0.167	100/400/12	33	1	A LM5072
TGP13-S011EP13LF	1:0.500:0.150:0.275	450/700/30/400	160	3	B TPS23750



HALO 7W, 3.3Vout, Power Transformers (EP10)

Power Over Ethernet, DC/DC Converter


HALO Electronics offers a broad line of power transformers designed for fly-back DC/DC converters used in Power over Ethernet (PoE) applications. These industrial temperature range transformers are UL recognized and are fully compliant to IEEE802.3af requirements for isolation and power ratings. This standard series is LEAD-free and RoHS compliant. Please contact your nearest HALO representative for custom designs.



MECHANICAL DIMENSIONS




CO-PLANARITY: 0.005 [0.13]




RECOMMENDED SOLDER PAD DIMENSIONS

DIMENSIONS: Inch [mm]
TOLERANCES: 0.006 inch if not specified

SCHEMATIC A



SCHEMATIC B



7W, 3.3Vout, Power Transformers (EP10)
Power Over Ethernet, DC/DC Converter

Electrical Specifications @ 25 °C

Isolation Voltage (PRI – SEC): 1,500Vrms
Operating Temp: -40 to +85 °C



Part Number	Turns Ratio PRI:AUX:SEC:DRV	DCR (mΩ max) PRI/AUX/SEC/DRV	PRI OCL (μH ±10%)	PRI LL (μH Max)	IC SCHE. P/N
TGP7-S002EP10LF	1:0.208:0.083	450/400/12	145	4	A LTC4267
TGP7-S006EP10LF	1: 0.500:0.167	100/400/10	33	1	A LM5072
TGP7-S010EP10LF	1:0.500:0.150:0.275	450/700/30/400	160	3	B TPS23750


HALO

3W, 3.3Vout, Power Transformers (EP7) Power Over Ethernet, DC/DC Converter

HALO Electronics offers a broad line of power transformers designed for fly-back DC/DC converters used in Power over Ethernet (PoE) applications. These industrial temperature range transformers are UL recognized and are fully compliant to IEEE802.3af requirements for isolation and power ratings. This standard series is LEAD-free and RoHS compliant. Please contact your nearest HALO representative for custom designs.




MECHANICAL DIMENSIONS




RECOMMENDED SOLDER PAD DIMENSIONS

DIMENSIONS: Inch [mm]
TOLERANCES: 0.006 inch if not specified

SCHEMATIC A



SCHEMATIC B



3W, 3.3Vout, Power Transformers (EP7)
Power Over Ethernet, DC/DC Converter

Electrical Specifications @ 25 °C

Isolation Voltage (PRI – SEC): 1,500Vrms
Operating Temp: -40 to +85 °C



Part Number	Turns Ratio PRI:AUX:SEC:DRV	DCR (mΩ max) PRI/AUX/SEC/DRV	PRI OCL (μH ±10%)	PRI LL (μH Max) SCHE.	IC P/N
TGP3-S001EP7LF	1:0.208:0.083	1200/300/20	145	4 A	LTC4267
TGP3-S005EP7LF	1: 0.500:0.167	160/300/15	33	1 A	LM5072
TGP3-S009EP7LF	1:0.500:0.150:0.275	1000/550/50/300	160	3 B	TPS23750

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HALO Electronics:

[TGP13-S007EP13LF](#) [TGP13-S011EP13LF](#) [TGP3-S009EP7LF](#) [TGP3-S009EP7LFTR](#) [TGP13-S007EP13LFTR](#)
[TGP13-S011EP13LFTR](#) [TGP13-S008EFD15LF](#) [TGP13-S003EP13LF](#) [TGP3-S001EP7LF](#) [TGP7-S002EP10LF](#)
[TGP13-S004EFD15LF](#) [TGP7-S010EP10LF](#) [TGP7-S006EP10LF](#) [TGP13-S012EFD15LF](#) [TGP3-S005EP7LF](#)