iW600

Secondary-Side Voltage Positioning Controller

1 Description

The iW600 is a secondary-side voltage position controller to detect the voltage undershoot. It can be used in Dialog's primary-side control systems to achieve ultra-low no-load power consumption and fast dynamic load response. The iW600 operates in "Normally-OFF" mode with negligible power consumption during power supply normal steady state operation, while monitoring dynamic load change through the voltage on the secondary rectifier. A wake-up signal is transferred through the flyback power transformer to the primary side when a dynamic load change is detected. The iW600 eliminates loop compensation components and the optocoupler on the secondary side to minimize the bill of material cost.

2 Features

- Fast system output voltage detection
- Transmits detection signal to the primary side through flyback transformer
- Two-electrical-terminal connection simplifies system PCB layout

3 Applications

AC/DC adapters/chargers

- No external components
- Enables <10mW no-load power consumption in typical 5V-output systems

Company Confidential

Available in 3-lead SOT-23 and 2-lead DFN packages



Figure 3.1: iW600 Typical Application Circuit (Using iW1600 as Primary-Side Controller) (Achieving < 10mW No-load Power Consumption in 5V/2A 10W Adapter with Fast Dynamic Load Response)

iW600

Secondary-Side Voltage Positioning Controller



Company Confidential

4 Pinout Description





Figure 4.1: 3-Lead SOT-23 Package

Pin No.	Name	Туре	Pin Description					
1	STR	Power Input/ Analog Input/ Power Output	Stroke pin. Controller Power input and voltage monitoring input. It also builds in a open-drain circuit to drive the flyback power transformer when dynamic load is detected.					
2	GND	Ground	Ground.					
3	N/C	N/C	Not connected. Recommend design a solder pad and solder this pin on the printed circuit board for mechanical stability.					
Note 1: The N/C pin is only available in the 3-lead SOT-23 package.								

Product Summary

Company Confidential

Secondary-Side Voltage Positioning Controller

5 Absolute Maximum Ratings

Absolute maximum ratings are the parameter values or ranges which can cause permanent damage if exceeded. For maximum safe operating conditions, refer to Electrical Characteristics (Section 6).

Parameter	Symbol	Value	Units
Input voltage range	V _{STR}	-1 to 60	V
Continuous DC supply current at V_{STR} pin (V_{STR} = 60V)	I _{CC_OP}	1	mA
Open-draining pull-down pulse current (V _{STR} = 40V)		400	mA
Maximum junction temperature	T _{JMAX}	150	°C
Operating junction temperature	T _{JOPT}	-40 to 150	°C
Storage temperature	T _{STG}	-65 to 150	°C
Thermal resistance junction-to-ambient (SOT-23)	θ _{JA}	260	°C/W
Thermal resistance junction-to-ambient (DFN)	θ _{JA}	680	°C/W
ESD rating per JEDEC JESD22-A114	- V	±2,000	V
NOT			

Company Confidential

Secondary-Side Voltage Positioning Controller

6 Physical Dimensions

3-Lead SOT-23 Package



			C		
lodn	Inc	hes	Millimeters		
Syr	MIN	MAX	MIN	MAX	
А	0.035	0.044	0.89	1.11	
A1	0.001	0.004	0.01	0.10	
В	0.015	0.020	0.37	0.50	
С	0.003	0.007	0.09	0.18	
D	0.110	0.120	2.80	3.04	
E	0.083	0.104	2.10	2.64	
E 1	0.047	0.081	1.20	1.40	
e1	0.070	0.020	1.78	2.04	

Compliant to JEDEC Standard TO236

Controlling dimensions are in millimeters

This package is RoHS compliant, and conform to Halide free limits.

Soldering Temperature Resistance:

ARX

- [a] Package is IPC/JEDEC Std 020D Moisture Sensitivity Level 1
- [b] Package exceeds JEDEC Std No. 22-A111 for Solder Immersion resistance; packages can withstand 10 s immersion @ < 260 °C</p>

Dimension D does not include mold flash, protrusions or gate burrs. Mold flash, protrusions or gate burrs shall not exceed 0.25 mm per end. Dimension E1 does not include interlead flash or protrusion. Interlead flash or protrusion shall not exceed 0.25 mm per side.

Product Summary

Secondary-Side Voltage Positioning Controller



Company Confidential

2-Lead DFN Package



Note 1: Tape & Reel packing quantity is 3,000/reel. Minimum ordering quantity is 3,000.

Proc	luct	Summarv	,
1100		Guilling	

Secondary-Side Voltage Positioning Controller

Disclaimer

Information in this document is believed to be accurate and reliable. However, Dialog Semiconductor does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information. Dialog Semiconductor furthermore takes no responsibility whatsoever for the content in this document if provided by any information source outside of Dialog Semiconductor.

Dialog Semiconductor reserves the right to change without notice the information published in this document, including without limitation the specification and the design of the related semiconductor products, software and applications.

Applications, software, and semiconductor products described in this document are for illustrative purposes only. Dialog Semiconductor makes no representation or warranty that such applications, software and semiconductor products will be suitable for the specified use without further testing or modification. Unless otherwise agreed in writing, such testing or modification is the sole responsibility of the customer and Dialog Semiconductor excludes all liability in this respect.

Customer notes that nothing in this document may be construed as a license for customer to use the Dialog Semiconductor products, software and applications referred to in this document. Such license must be separately sought by customer with Dialog Semiconductor.

All use of Dialog Semiconductor products, software and applications referred to in this document are subject to Dialog Semiconductor's Standard Terms and Conditions of Sale, available on the company website (www.dialog-semiconductor.com) unless otherwise stated.

Dialog and the Dialog logo are trademarks of Dialog Semiconductor plc or its subsidiaries. All other product or service names are the property of their respective owners.

© 2018 Dialog Semiconductor. All rights reserved.

RoHS Compliance

Dialog Semiconductor's suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on a commute which a request.

Contacting Dialog Semiconductor

United Kingdom (Headquarters) Dialog Semiconductor (UK) LTD Phone: +44 1793 757700

Germany

Dialog Semiconductor GmbH Phone: +49 7021 805-0

The Netherlands Dialog Semiconductor B.V. Phone: +31 73 640 8822

Email info_pcbg@diasemi.com

Product Summary

North America Dialog Semiconductor Inc. Phone: +1 408 845 8500

Japan

Dialog Semiconductor K. K. Phone: +81 3 5425 4567

Taiwan

Dialog Semiconductor Taiwan Phone: +886 281 786 222

Web site

www.dialog-semiconductor.com

Singapore Dialog Semiconductor Singapore

Phone: +65 64 8499 29

Hong Kong Dialog Semiconductor Hong Kong Phone: +852 3769 5200

Korea Dialog Semiconductor Korea Phone: +82 2 3469 8200

China (Shenzhen) Dialog Semiconductor China Phone: +86 755 2981 3669

China (Shanghai) Dialog Semiconductor China Phone: +86 21 5424 9058

10-Mar-2018



Rev. 1.1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialog Semiconductor: <u>iW600-00-ST3</u>