

SmartBond™ DA14585 Range Extender Daughterboard

Boost the range of your Bluetooth® low energy applications

Bluetooth® low energy is a key technology for the Internet of Things. Some IoT applications require longer distance to be covered by the Bluetooth connection. For example, Smart Home networks need to be carefully designed to ensure all nodes can communicate with the gateway. Proximity tags and beacons could be even more useful if they worked over greater distances, allowing single nodes to cover entire commercial or industrial sites.

By combining Dialog's best-in-class Bluetooth low energy chips with a high-efficiency RF Power Amplifier front-end-module, Dialog's range extender offers you optimal range without compromising on power consumption and data rate. Dialog's **SmartBond™ DA14585 Range Extender** kit allows the range of Bluetooth low energy communications to be increased in software-selectable steps without compromising on data rate and maintain best in class overall power consumption. The resulting solution meets all Bluetooth low energy and regulatory requirements.

The Range Extender daughterboard is provided as an optional extra for the DA14585 Pro Development Kit, featuring the Skyworks SKY66111 discrete power amplifier. The optimized board design allows output power to be scaled by software in 2 dBm steps from +0 dBm to +9.3 dBm (enough for whole house coverage indoors). So system developers have freedom to balance range and overall power consumption. Crucially, the solution maintains the standard Bluetooth low energy data rate. It can also be powered from single coin cell ensuring the smallest systems.


Pre-certified to FCC and CE standards, the **SmartBond™ DA14585 Range Extender** takes the design effort out of developing long-range Bluetooth low energy applications. So manufacturers can get to market faster with fewer design resources.


Benefits

- ▶ Extends range at the lowest power consumption without compromising data rate
- ▶ Runs on single coin cell battery
- ▶ Accelerates time to market

Applications



- All Bluetooth low energy applications that require extended range like;
- ▶ Smart Home applications
 - ▶ Beacons
 - ▶ Proximity Tags and much more



 dialog SEMICONDUCTOR		DA14585	
ARM M0™ CPU		XTAL 16M	XTAL 32K
SWD	OTP 64 kB	RC32KHz	
UARTx2 SPI I2C		RC16KHz	
		RCX	
ADC	RAM 32 kB	BLE 5.0 MAC Ready	Digital PHY RADIO
KEYBOARD	RAM 16 kB		
WAKEUP	RAM 16 kB		
4-CH DMA	RAM 32 kB		
QDEC		DCDC BUCK	
TIMERS	ROM 128kB	DCDC BOOST	
PCM/12S		LDOs	
PDM			
GPIO matrix			

Features

- ▶ Software programmable output power up to +9.3 dBm in steps of 2 dBm
- ▶ FCC, ETSI and Bluetooth® requirements compliant
- ▶ Receiver Sensitivity < -91dBm
- ▶ Tx Power consumption < 18 mA at +9.3 dBm @ 3 V
- ▶ Rx Power consumption < 6 mA @ -91 dBm @ 3 V
- ▶ Extended sleep mode < 5uA @ 3V
- ▶ Operating voltage 1.8 – 3.6 V
- ▶ Supports coin cell battery (typ 3.0 V)
- ▶ 2 layer FR-4 PCB
- ▶ Integrated Printed Antenna (IFA) and RF connector for RF measurements
- ▶ Provision for external battery connector available
- ▶ 21 GPIOs available
- ▶ Key signals available through test points
- ▶ Operating temperature -40 to +85C
- ▶ Compatible with DA14585 Development Kit Pro
- ▶ Dialog's SmartBond™ DA14585 complies with Bluetooth 5.0
- ▶ 16 MHz 32 bit ARM Cortex-M0
- ▶ Integrated DCDC converter
- ▶ Supports up to 8 Bluetooth® low energy connections



For more information and purchasing please visit
<https://support.dialog-semiconductor.com/connectivity>

Dialog Semiconductor Worldwide Sales Offices - www.dialog-semiconductor.com email: info@diasemi.com

United Kingdom
 Phone: +44 1793 757700

The Netherlands
 Phone: +31 73 640 88 22

Japan
 Phone: +81 3 5769 5100

Singapore
 Phone: +65 648 499 29

Korea
 Phone: +82 2 3469 8200

Germany
 Phone: +49 7021 805-0

North America
 Phone: +1 408 845 8500

Taiwan
 Phone: +886 281 786 222

Hong Kong
 Phone: +852 3769 5200

China (Shenzhen)
 Phone: +86 755 2981 3669

China (Shanghai)
 Phone: +86 21 5424 9058

This publication is issued to provide outline information only, which unless agreed by Dialog Semiconductor may not be used, applied, or reproduced for any purpose or be regarded as a representation relating to products. All use of Dialog Semiconductor products, software and applications referred to in this document are subject to Dialog Semiconductor's [Standard Terms and Conditions of Sale](#), available on the company website (www.dialog-semiconductor.com) unless otherwise stated.

Dialog and the Dialog logo are trademarks of Dialog Semiconductor plc or its subsidiaries. All other product or service names are the property of their respective owners.

© Copyright 2017 Dialog Semiconductor. All rights reserved. 1117CREA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Dialog Semiconductor:](#)

[DA14585-00000ATREXDB-P](#)