



## XL+ | CF 5.0 | CF Card

SMART's XL+ CF Cards offer reliable, high performance in an industry standard CompactFlash® (CF) form factor. The industrial-grade XL+ CF Card products specifically support OEM markets of networking, telecommunication and data communication, embedded computing, medical, and industrial applications. SMART has designed their CF Cards using Single-Level Cell (SLC) Flash technology for enhanced data integrity and life time expectations in critical embedded applications.

SMART's CF Card product line supports Self-Monitoring Analysis and Reporting Technology (S.M.A.R.T.), which is designed to reduce field failures and unscheduled service maintenance. S.M.A.R.T. enables a reliable monitoring application that efficiently supports CF Cards in the field and guarantees 24/7 service availability.



### Features & Benefits

- Highly Reliable SLC NAND Flash Technology
- Static and Dynamic Wear-Leveling
- Field Upgradeable Firmware
- RoHS-6 Compliant
- Self-Monitoring Analysis and Reporting Technology (S.M.A.R.T.) Support

### Applications

- Communications
- Defense
- Gaming
- Industrial Control Equipment
- Networking
- Printers

### Product Family Overview

Form Factor	Capacity	Sequential Performance
CF 5.0 CF Card	512MB to 64GB	Up to 55MB/s Read Up to 27MB/s Write

## Specifications

	XL+   CF 5.0   CF Card
NAND Type	SLC
<b>Performance</b>	
Sequential Read (maximum)	Up to 55MB/s
Sequential Write (maximum)	Up to 27MB/s
<b>Reliability</b>	
Data Reliability	< 1 Non-Recoverable Error in 10 <sup>14</sup> bits read
Data Retention	10 years >90% life remaining 1 year at the end of life
Endurance	TBW up to 3TB per 1GB capacity
<b>Power</b>	
VCC	5.0V+10% 3.3V+5%
Read	< 200mA
Write	< 200mA
Idle	< 4mA
<b>Environmental</b>	
Shock (operational)	50G @ 11ms
Vibration	15G peak to peak
Operating Temperature	Commercial: 0°C to +70°C Industrial: -40°C to +85°C
Storage Temperature	-55°C to +85°C
Humidity	5% to 95%
<b>Physical</b>	
Length	36.4mm
Width	42.8mm
Thickness	3.3mm

## Ordering Information

Part Number	Density
<b>XL+   CF 5.0   CF Card</b> <b>Commercial Operating Temperature (0°C to +70°C)</b>	
SG9CF64GHYDD	64GB
SG9CF32GHYDD	32GB
SG9CF16GHYDC	16GB
SG9CF8GHYDB	8GB
SG9CF4GHYDA	4GB
SG9CF2GHYD9	2GB
SG9CF1GHYD4	1GB
SG9CF512HYD2	512MB
<b>XL+   CF 5.0   CF Card</b> <b>Industrial Operating Temperature (-40°C to +85°C)</b>	
SG9CF64GHYDDI	64GB
SG9CF32GHYDDI	32GB
SG9CF16GHYDCI	16GB
SG9CF8GHYDBI	8GB
SG9CF4GHYDAI	4GB
SG9CF2GHYD9I	2GB
SG9CF1GHYD4I	1GB
SG9CF512HYD2I	512MB



For more information, please visit: [www.smartm.com](http://www.smartm.com)

*\*Product images are for promotional purposes only. Labels may not be representative of the actual product.*

### Headquarters/North America:

T: (+1) 800-956-7627 • T: (+1) 510-623-1231  
F: (+1) 510-623-1434 • E: [info@smartm.com](mailto:info@smartm.com)

### Latin America:

T: (+55) 11 4417-7200 • E: [sales.br@smartm.com](mailto:sales.br@smartm.com)

### Asia/Pacific:

T: (+65) 6678-7670 • E: [sales.asia@smartm.com](mailto:sales.asia@smartm.com)

### EMEA:

T: (+44) 0 7826-064-745 • E: [sales.euro@smartm.com](mailto:sales.euro@smartm.com)

### Customer Service:

T: (+1) 510-623-1231 • E: [customers@smartm.com](mailto:customers@smartm.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SMART Modular Technologies:](#)

[SG9CF64GHYDDI](#) [SG9CF4GHYDA](#) [SG9CF4GHYDAI](#)