

## Co-Solvent Low Evaporating Flux Remover in 30ml (1.0oz) Squeeze Bottle w/tip

### Product Highlights


Powerful Co-Solvent Flux Remover  
Low Evaporating  
Low Surface Tension to Clean Under Small Parts

Environmentally-Friendly  
Low Ozone Depletion, Low Toxicity  
RoHS 3 and REACH compliant

### Specifications

Boiling Point:	175-215 °C
Flash Point:	77 °C
Vapor Pressure:	0.1 kPa
Liquid Density:	0.825 g/cm <sup>3</sup> (at 20°C)
Kinematic Viscosity:	1.6 cSt (mm <sup>2</sup> /s)
Surface Tension:	14 mN/m
Relative Evaporation Rate (RER):	0.06 nBuAc-1
Dielectric Strength (0.1" gap):	>25 kV
Global Warming Potential:	<25 GWP
Ozone Depletion Potential:	0
Color:	Clear
Miscibility in Water:	Not miscible
Net Weight:	24.75g
Net Volume:	30ml
Packaging:	30ml Squeeze Bottle

### Co-solvent De-fluxing Process:



### Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F).

### Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.

### Conforms to the following Industry Standards:

RoHS 3 Directive (EU) 2015/863:

Yes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Chip Quik:

COSOLV175-1.0