

REL0 No-Clean Water-Washable Tack Flux in 5cc/5g Luer Lock Manual Syringe w/tips**Product Highlights**

Ideal for all rework, solder, de-solder and reflow applications

Non-corrosive, non-conductive, no-clean, water-washable

Tack flux will not run all over PCB when applied

Has a pleasant odor

Excellent wetting

Easily cleaned with isopropyl alcohol (IPA) or water

Attachment of BGA spheres

Soldering flip chip components

Long stencil life

Wide process window

Clear residue

For Leaded and Lead-Free applications

RoHS 3 and REACH compliant

**Specifications**

Flux Type:	Synthetic No-Clean Water-Washable (for Leaded and Lead-Free applications)
Flux Classification:	REL0
Flux Activation Temperature:	140°C (284°F)
Packaging:	5cc/5g Luer Lock Manual Syringe
Shelf Life:	Refrigerated >24 months, Unrefrigerated >24 months

Stencil Life

>8 hours @ 20-50% RH 22-28°C (72-82°F)

>4 hours @ 50-70% RH 22-28°C (72-82°F)

Stencil Cleaning

Automated stencil cleaning systems for both stencil and misprinted boards. Manual cleaning using isopropyl alcohol (IPA).

Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). Do not freeze. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.

Conforms to the following Industry Standards:

J-STD-004B, Amendment 1 (Solder Fluxes):

Yes

RoHS 3 Directive (EU) 2015/863:

Yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)
[SMD4300-5M](#)