


THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!




1. Rating:300V 15A(UL)
2. Insulation Withstanding Voltage:AC2000V/MIN
3. Insulation Resistance: $\geq 500M\Omega$ or more at DC500V
4. Temperature Range: $-33^{\circ}C/+105^{\circ}C$
5. Screw Torque Vlaue:3.5lbf-in(UL)
6. Suitable Electric Wire: 14-22AWG



ON-SHORE TECHNOLOGY, INC.

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE	ES0800 Series - 8.0mm Euro Strip, Wire guard, flat base						
PART NO.	ES0800/XXDSFB <small>DOX - number of poles per row</small>			DWG NO.	ES0800/XXDSFB.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN		5020		Tolerance
KSZ 2007.08.01	KSZ 2007.08.01	KSZ 2007.08.01	KSZ 2007.08.01		UNIT: mm		X ±015
					SCALE: NONE		.XX ±0.075
					SHEET: 01/01		REV: A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adafruit:](#)

[677](#)