

CMOTVS5V7**SURFACE MOUNT SILICON
TRANSIENT VOLTAGE SUPPRESSOR****SOD-523 CASE**www.centralemi.com**DESCRIPTION:**

The CENTRAL SEMICONDUCTOR CMOTVS5V7 is a Transient Voltage Suppressor (TVS) with exceptionally low leakage current characteristics. Packaged in the SOD-523 surface mount case, this space saving device is designed to protect sensitive equipment against ESD damage.

MARKING CODE: 57**APPLICATIONS:**

- User interface protection
- Power rail protection
- Voltage clamping

FEATURES:

- Low leakage current
- 15kV ESD Protection
- Space saving SOD-523 package

MAXIMUM RATINGS: ($T_A=25^{\circ}\text{C}$)Peak Power Dissipation (8x20 μs)

ESD Voltage (IEC 61000-4-2, Air)

Operating and Storage Junction Temperature

SYMBOL P_{PK}

66

 V_{ESD}

15

 T_J, T_{stg}

-55 to +150

UNITS

W

kV

 $^{\circ}\text{C}$ **ELECTRICAL CHARACTERISTICS:** ($T_A=25^{\circ}\text{C}$) $V_F=1.2\text{V MAX @ } I_F=20\text{mA}$


Maximum Reverse Stand-off Voltage V_{RWM}	Breakdown Voltage $V_{BR} @ I_T$		Test Current I_T	Maximum Reverse Leakage Current $I_R @ V_{RWM}$	Maximum Clamping Voltage $V_C @ I_{PP}$	Peak Pulse Current I_{PP}	Typical Junction Capacitance @ 0V Bias C_J
V	MIN V	MAX V	mA	μA	V	A	pF
4.0	5.7	6.7	5.0	0.1	12	5.5	35

CMOTVS5V7

**SURFACE MOUNT SILICON
TRANSIENT VOLTAGE SUPPRESSOR**



SOD-523 CASE - MECHANICAL OUTLINE



LEAD CODE:

- 1) Cathode
- 2) Anode

MARKING CODE: 57

SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.020	0.031	0.50	0.80
B	0.008	0.016	0.20	0.40
C	0.002	0.008	0.05	0.20
D	0.028	0.035	0.70	0.90
E	0.008	0.014	0.20	0.35
F	0.039	0.055	1.00	1.40
G	0.055	0.071	1.40	1.80
H	0.016		0.40	

SOD-523 (REV: R3)






R2 (25-February 2013)

CMOTVS5V7

**SURFACE MOUNT SILICON
TRANSIENT VOLTAGE SUPPRESSOR**



TYPICAL ELECTRICAL CHARACTERISTICS



R2 (25-February 2013)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Central Semiconductor:

CMOTVS5V7 TR PBFREE