## CEN-U05 CEN-U06 CEN-U07 NPN CEN-U55 CEN-U56 CEN-U57 PNP

## COMPLEMENTARY SILICON POWER TRANSISTORS



 $V_{CE}$ =1.0V,  $I_{C}$ =250mA

 $V_{CE}$ =1.0V,  $I_{C}$ =50mA

 $V_{CE}=1.0V, I_{C}=250mA$ 

 $V_{CE}$ =1.0V,  $I_{C}$ =500mA

 $V_{CB}$ =10V,  $I_E$ =0, f=1.0MHz

 $V_{CE}$ =5.0V,  $I_{C}$ =200mA, f=100MHz

#### **APPLICATIONS:**

V<sub>BE(ON)</sub>

hFE

hFE

hFE

f<sub>T</sub> C<sub>ob</sub>

• Designed for general purpose high voltage amplifiers and drivers



www.centralsemi.com

## **DESCRIPTION:**

The CENTRAL SEMICONDUCTOR CEN-U05/U55 series types are complementary silicon power transistors designed for general purpose audio amplifier applications. These devices are electrically equivalent to National Semiconductor's NSDU05, NSDU06, NSDU07, NSDU55, NSDU56, and NSDU57.

### **MARKING: FULL PART NUMBER**

#### **FEATURES:**

• High Collector-Emitter breakdown voltage

1.2

30

• High 10W power dissipation

MAXIMUM RAT	<b>FINGS:</b> (T <sub>C</sub> =25°C) Voltage	SYMBOL V <sub>CBO</sub>	CEN-U05 CEN-U55 60	CEN-U06 CEN-U56 80	CEN-U07 CEN-U57 100	UNITS
Collector-Emitte	er Voltage	VCEO	60	80	100	V
Emitter-Base Voltage		$V_{EBO}$		4.0		V
Continuous Col	lector Current	IC		2.0		Α
Power Dissipati	on	$P_{D}$		10		W
Power Dissipati	on (T <sub>A</sub> =25°C)	$P_{D}$		1.75		W
Operating and S	Storage Junction Temperature	T <sub>J</sub> , T <sub>stg</sub>		-65 to +150		°C
Thermal Resistance		$\Theta_{JA}$		71.4		°C/W
Thermal Resistance		$\Theta$ JC		12.5		°C/W
ELECTRICAL (	nitter-Base Voltage $V_{EBO}$ 4.0 V  Intinuous Collector Current $I_C$ 2.0 A  Inter-Base Voltage $V_{EBO}$ 4.0 V  Intinuous Collector Current $I_C$ 2.0 A  Inver Dissipation $V_{EBO}$ 10 W  Inver Dissipation $V_{EBO}$ 1.75 W  Inver Dissipation $V$					
SYMBOL			,			UNITS
ICBO	V <sub>CB</sub> =Rated V <sub>CBO</sub>			0.1		μΑ
I <sub>EBO</sub>	V <sub>EB</sub> =4.0V			100		μΑ
BVCEO	I <sub>C</sub> =1.0mA (CEN-U05, CEN-U55)	60				V
BVCEO	I <sub>C</sub> =1.0mA (CEN-U06, CEN-U56)	80				V
BVCEO	I <sub>C</sub> =1.0mA (CEN-U07, CEN-U57)	100				V
V <sub>CE</sub> (SAT)	I <sub>C</sub> =250mA, I <sub>B</sub> =10mA			0.5		V
VCE(SAT)	$I_C$ =250mA, $I_B$ =25mA			0.35		V

80

50

20

50

R2 (20-January 2012)

٧

MHz


рF


# CEN-U05 CEN-U06 CEN-U07 NPN CEN-U55 CEN-U56 CEN-U57 PNP

# COMPLEMENTARY SILICON POWER TRANSISTORS



## **TO-202 CASE - MECHANICAL OUTLINE**





## LEAD CODE:

- 1) Emitter
- 2) Base
- 3) Collector

Tab is common to pin 3

### MARKING:

FULL PART NUMBER

DIMENSIONS								
	INCHES		MILLIMETERS					
SYMBOL	MIN	MAX	MIN	MAX				
Α	0.055	0.071	1.40	1.80				
В	0.016	0.024	0.40	0.60				
С	0.173	0.181	4.40	4.60				
D	0.374	0.413	9.50	10.5				
E	0.118	0.154	3.00	3.90				
F (DIA)	0.124	0.150	3.15	3.80				
G	0.035	0.055	0.90	1.40				
Н	0.023	0.031	0.59	0.80				
J	0.094	0.106	2.39	2.69				
K	0.459	0.559	11.66	14.21				
Ĺ	0.280	0.346	7.12	8.80				
М	0.406	0.531	10.3	13.5				
N	0.024	0.059	0.60	1.50				
TO-202 (REV: R2)								

R2 (20-January 2012)

### **OUTSTANDING SUPPORT AND SUPERIOR SERVICES**



#### PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- · Inventory bonding
- · Consolidated shipping options

- · Custom bar coding for shipments
- · Custom product packing

#### **DESIGNER SUPPORT/SERVICES**

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free guick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- · Custom electrical curves
- · Environmental regulation compliance
- · Customer specific screening
- · Up-screening capabilities

- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- · Application and design sample kits
- Custom product and package development

#### REQUESTING PRODUCT PLATING

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- 2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

#### **CONTACT US**

### Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA

Main Tel: (631) 435-1110 Main Fax: (631) 435-1824

Support Team Fax: (631) 435-3388

www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

**Worldwide Distributors:** 

www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: <a href="https://www.centralsemi.com/terms">www.centralsemi.com/terms</a>

www.centralsemi.com (001)

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Central Semiconductor: CEN-U57 PBFREE