

CMPSH05-4

SURFACE MOUNT SILICON
HIGH CURRENT, LOW V_F
SCHOTTKY DIODE



SOT-23 CASE



www.centrasemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMPSH05-4 is a high current, low V_F 40 volt Schottky diode packaged in a space saving SOT-23 surface mount case. This device has been designed for small signal general purpose applications when small size and operational efficiency are prime requirements.

MARKING CODE: C054

FEATURES:

- Low $V_F = 0.35V$ max @ 100mA
- $V_{RRM} = 40V$
- $I_F = 500mA$

MAXIMUM RATINGS: ($T_A = 25^\circ C$)

Peak Repetitive Reverse Voltage
Continuous Forward Current
Peak Repetitive Forward Current, $t_p \leq 1.0ms$
Peak Forward Surge Current, $t_p = 8.0ms$
Power Dissipation
Operating and Storage Junction Temperature
Thermal Resistance

SYMBOL

V_{RRM}	40
I_F	500
I_{FRM}	3.5
I_{FSM}	10
P_D	350
T_J, T_{stg}	-65 to +150
Θ_{JA}	357

UNITS

V
mA
A
A
mW
 $^\circ C$
 $^\circ C/W$

ELECTRICAL CHARACTERISTICS: ($T_A = 25^\circ C$ unless otherwise noted)


SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS
I_R	$V_R = 10V$		30	μA
I_R	$V_R = 30V$		100	μA
BV_R	$I_R = 500\mu A$	40		V
V_F	$I_F = 100\mu A$		0.13	V
V_F	$I_F = 1.0mA$		0.21	V
V_F	$I_F = 10mA$		0.27	V
V_F	$I_F = 100mA$		0.35	V
V_F	$I_F = 500mA$		0.47	V
C_J	$V_R = 1.0V, f = 1.0MHz$		50	pF

CMP5H05-4

SURFACE MOUNT SILICON
HIGH CURRENT, LOW V_F
SCHOTTKY DIODE



SOT-23 CASE - MECHANICAL OUTLINE



LEAD CODE:

- 1) Anode
- 2) No Connection
- 3) Cathode

MARKING CODE: C054

DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.003	0.007	0.08	0.18
B	0.006	-	0.15	-
C	-	0.005	-	0.13
D	0.035	0.043	0.89	1.09
E	0.110	0.120	2.80	3.05
F	0.075		1.90	
G	0.037		0.95	
H	0.047	0.055	1.19	1.40
I	0.083	0.098	2.10	2.49
J	0.014	0.020	0.35	0.50

SOT-23 (REV: R3)





R3 (8-January 2018)

CMP5H05-4

SURFACE MOUNT SILICON
HIGH CURRENT, LOW V_F
SCHOTTKY DIODE



TYPICAL ELECTRICAL CHARACTERISTICS





R3 (8-January 2018)

CMP5H05-4

SURFACE MOUNT SILICON
HIGH CURRENT, LOW V_F
SCHOTTKY DIODE



TYPICAL ELECTRICAL CHARACTERISTICS



R3 (8-January 2018)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Central Semiconductor:

[CMPSH05-4 TR](#) [CMPSH05-4 BK](#)