

CentralTM Semiconductor Corp.

145 Adams Avenue, Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824

Manufacturers of World Class Discrete Semiconductors

2N4264

NPN SILICON TRANSISTOR

JEDEC TO-92 CASE

DESCRIPTION

The CENTRAL SEMICONDUCTOR 2N4264 type is a Silicon NPN Transistors designed for high speed switching applications.

MAXIMUM RATINGS (T_A = 25°C)

	SYMBOL		UNITS
Collector-Base Voltage	V _{CB0}	30	V
Collector-Emitter Voltage	V _{CEO}	15	V
Emitter-Base Voltage	V _{EBO}	6.0	V
Collector Current	I _C	200	mA
Power Dissipation	P _D	625	mW
Operating and Storage			
Junction Temperature	T _J , T _{stg}	-55 to +150	°C
Thermal Resistance	θ _{JA}	200	°C/W

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS
I _{CEV}	V _{CE} = 12V, V _{BE(OFF)} = 0.25V		0.1	uA
I _{CEV}	V _{CE} = 12V, V _{BE(OFF)} = 0.25V, T _A = 100°C		10	uA
BV _{CEO}	I _C = 1.0mA	15		V
BV _{CBO}	I _C = 10uA,	20		V
BV _{EBO}	I _E = 10uA	6.0		V
V _{CE(SAT)}	I _C = 10mA, I _B = 1.0mA		0.22	V
V _{CE(SAT)}	I _C = 100mA, I _B = 10mA		0.35	V
V _{BE(SAT)}	I _C = 10mA, I _B = 1.0mA	0.65	0.80	V
V _{BE(SAT)}	I _C = 100mA, I _B = 10mA	0.75	0.95	V
h _{FE}	V _{CE} = 1.0V, I _C = 1.0mA	25		-
h _{FE}	V _{CE} = 1.0V, I _C = 10mA	40	160	-
h _{FE}	V _{CE} = 1.0V, I _C = 30mA	40		-
h _{FE}	V _{CE} = 1.0V, I _C = 100mA	30		-
h _{FE}	V _{CE} = 1.0V, I _C = 200mA	20		-
f _T	V _{CE} = 10V, I _C = 10mA, f = 100MHz	350		MHz
C _{ib}	V _{BE} = 0.5V, I _C = 0, f = 1.0MHz		8.0	pF
C _{ob}	V _{CB} = 5.0V, I _E = 0, f = 1.0MHz		4.0	pF

(Continued on Reverse Side)

ELECTRICAL CHARACTERISTICS (Continued)

<u>SYMBOL</u>	<u>TEST CONDITIONS</u>	<u>MIN</u>	<u>MAX</u>	<u>UNITS</u>
t_d	$V_{CC} = 10V, V_{BE(OFF)} = 2.0V, I_C = 100mA, I_{B1} = 10mA$		8.0	ns
t_r	$V_{CC} = 10V, V_{BE(OFF)} = 2.0V, I_C = 100mA, I_{B1} = 10mA$		15	ns
t_s	$V_{CC} = 10V, I_C = 10mA, I_{B1} = I_{B2} = 10mA$		20	ns
t_f	$V_{CC} = 10V, I_C = 100mA, I_{B1} = I_{B2} = 10mA$		15	ns
t_{on}	$V_{CC} = 3.0V, V_{BE(OFF)} = 1.5V, I_C = 10mA, I_{B1} = 3.0mA$		25	ns
t_{off}	$V_{CC} = 3.0V, I_C = 10mA, I_{B1} = 3.0mA, I_{B2} = 1.5mA$		35	ns
Q_T	$V_{CC} = 3.0V, I_C = 10mA, I_B = 1.0mA$		80	pC

Central[™]
Semiconductor Corp.

145 Adams Avenue
Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824
www.centrasemi.com

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Central Semiconductor:](#)

[2N4264 TIN/LEAD](#)