

1N5283 THRU 1N5314**SILICON CURRENT LIMITING DIODES**
www.centra-semi.com
DESCRIPTION:

The CENTRAL SEMICONDUCTOR 1N5283 series types are silicon field effect current regulator diodes designed for applications requiring a constant current over a wide voltage range. These devices are manufactured in the cost effective DO-35 double plug case which provides many benefits to the user, including space savings and improved thermal characteristics. Special selections of I_P (regulator current) are available for critical applications.

**DO-35 CASE****FEATURES:**

- High Reliability
- Superior Lot To Lot Consistency
- Special Selections Available
- Surface Mount Devices Available

MAXIMUM RATINGS: ($T_L=75^\circ\text{C}$)

Peak Operating Voltage

Power Dissipation

Operating and Storage Junction Temperature

SYMBOL P_{OV} P_D T_J, T_{stg}

100

600

-65 to +200

UNITS

V

mW

 $^\circ\text{C}$ **ELECTRICAL CHARACTERISTICS:** ($T_A=25^\circ\text{C}$)

Type	Regulator Current (Note 1) $I_P @ V_T=25\text{V}$			Minimum Dynamic Impedance $Z_T @ V_T=25\text{V}$	Minimum Knee Impedance $Z_K @ V_K=6.0\text{V}$	Maximum Limiting Voltage $V_L @ I_L=0.8 \times I_P \text{ MIN}$
	MIN mA	NOM mA	MAX mA	MΩ	MΩ	V
1N5283	0.187	0.22	0.253	25	2.75	1.0
1N5284	0.204	0.24	0.276	19	2.35	1.0
1N5285	0.230	0.27	0.311	14	1.95	1.0
1N5286	0.255	0.30	0.345	9.0	1.60	1.0
1N5287	0.281	0.33	0.380	6.6	1.35	1.0
1N5288	0.332	0.39	0.449	4.1	1.00	1.05
1N5289	0.366	0.43	0.495	3.3	0.87	1.05
1N5290	0.400	0.47	0.541	2.7	0.75	1.05
1N5291	0.476	0.56	0.644	1.90	0.56	1.10
1N5292	0.527	0.62	0.713	1.55	0.47	1.13
1N5293	0.578	0.68	0.782	1.35	0.40	1.15
1N5294	0.638	0.75	0.863	1.15	0.335	1.20
1N5295	0.697	0.82	0.943	1.00	0.29	1.25
1N5296	0.774	0.91	1.05	0.88	0.24	1.29
1N5297	0.850	1.00	1.15	0.80	0.205	1.35
1N5298	0.935	1.10	1.27	0.70	0.18	1.40

Notes: (1) Pulsed Method: Pulse Width (ms) = 27.5 divided by I_P NOM (mA)

R4 (7-February 2013)

1N5283 THRU 1N5314
SILICON CURRENT LIMITING DIODES



ELECTRICAL CHARACTERISTICS - Continued: ($T_A=25^\circ\text{C}$)

Type	Regulator Current (Note 1) $I_P @ V_T=25V$			Minimum Dynamic Impedance $Z_T @ V_T=25V$	Minimum Knee Impedance $Z_K @ V_K=6.0V$	Maximum Limiting Voltage $V_L @ I_L=0.8 \times I_P \text{ MIN}$
	MIN mA	NOM mA	MAX mA	MΩ	MΩ	V
1N5299	1.02	1.20	1.38	0.640	0.155	1.45
1N5300	1.11	1.30	1.50	0.580	0.135	1.50
1N5301	1.19	1.40	1.61	0.540	0.115	1.55
1N5302	1.28	1.50	1.73	0.510	0.105	1.60
1N5303	1.36	1.60	1.84	0.475	0.092	1.65
1N5304	1.53	1.80	2.07	0.420	0.074	1.75
1N5305	1.70	2.00	2.30	0.395	0.061	1.85
1N5306	1.87	2.20	2.53	0.370	0.052	1.95
1N5307	2.04	2.40	2.76	0.345	0.044	2.00
1N5308	2.30	2.70	3.11	0.320	0.035	2.15
1N5309	2.55	3.00	3.45	0.300	0.029	2.25
1N5310	2.81	3.30	3.80	0.280	0.024	2.35
1N5311	3.06	3.60	4.14	0.265	0.020	2.50
1N5312	3.32	3.90	4.49	0.255	0.017	2.60
1N5313	3.66	4.30	4.95	0.245	0.014	2.75
1N5314	4.00	4.70	5.41	0.235	0.012	2.90

DO-35 CASE - MECHANICAL OUTLINE



DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.018	0.022	0.46	0.56
B	0.120	0.200	3.05	5.08
C	0.060	0.090	1.52	2.29
D	1.000	-	25.40	-

DO-35 (REV: R1)

R1

R4 (7-February 2013)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centalsemi.com

Worldwide Field Representatives:
www.centalsemi.com/wwreps

Worldwide Distributors:
www.centalsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centalsemi.com/terms

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Central Semiconductor:

<u>1N5305 BK TIN/LEAD</u>	<u>1N5313 BK TIN/LEAD</u>	<u>1N5311 TR TIN/LEAD</u>	<u>1N5310 BK TIN/LEAD</u>	<u>1N5311 TR PBFREE</u>
<u>1N5313 TR TIN/LEAD</u>	<u>1N5307 BK TIN/LEAD</u>	<u>1N5309 TR TIN/LEAD</u>	<u>1N5308 TR TIN/LEAD</u>	<u>1N5312 TR TIN/LEAD</u>
<u>1N5305 TR TIN/LEAD</u>	<u>1N5312 BK TIN/LEAD</u>	<u>1N5308 BK TIN/LEAD</u>	<u>1N5307 TR TIN/LEAD</u>	<u>1N5309 BK TIN/LEAD</u>
<u>1N5310 TR TIN/LEAD</u>	<u>1N5314 TR TIN/LEAD</u>	<u>1N5311 BK TIN/LEAD</u>	<u>1N5314 BK TIN/LEAD</u>	