

1N957B THRU 1N992B

SILICON ZENER DIODE  
6.8 VOLTS THRU 200 VOLTS  
500mW, 5% TOLERANCE



DO-35 CASE



www.centrasemi.com

#### DESCRIPTION:

The CENTRAL SEMICONDUCTOR 1N957B Series Silicon Zener Diode is a high quality voltage regulator designed for use in industrial, commercial, entertainment and computer applications.

**MARKING:** Devices shall either be marked with the prefix 'C' followed by the full part number or by the marking code in the Electrical Characteristics Table.

#### MAXIMUM RATINGS: ( $T_L=75^\circ\text{C}$ )

Power Dissipation

Operating and Storage Junction Temperature

$V_Z$  Tolerance: Part number with "B" suffix

$V_Z$  Tolerance: Part number with "C" suffix

$V_Z$  Tolerance: Part number with "D" suffix

#### SYMBOL

$P_D$

$T_J, T_{stg}$

500

-65 to +200

$\pm 5$

$\pm 2$

$\pm 1$

#### UNITS

mW

$^\circ\text{C}$

%

%

%

#### ELECTRICAL CHARACTERISTICS: ( $T_A=25^\circ\text{C}$ ) $V_F=1.5\text{V MAX @ } I_F=200\text{mA}$ (for all types)

| TYPE   | ZENER VOLTAGE<br>$V_Z @ I_{ZT}$ |     |       | TEST CURRENT | MAXIMUM ZENER IMPEDANCE |                   |               | MAXIMUM REVERSE CURRENT |      | MAXIMUM ZENER CURRENT | MARKING CODE |  |
|--------|---------------------------------|-----|-------|--------------|-------------------------|-------------------|---------------|-------------------------|------|-----------------------|--------------|--|
|        | MIN                             | NOM | MAX   | $I_{ZT}$     | $Z_{ZT} @ I_{ZT}$       | $Z_{ZK} @ I_{ZK}$ | $I_R @ V_R$   | $I_{ZM}$                |      |                       |              |  |
|        | V                               | V   | V     | mA           | $\Omega$                | $\Omega$          | $\mu\text{A}$ | V                       | mA   |                       |              |  |
| 1N957B | 6.460                           | 6.8 | 7.140 | 18.5         | 4.5                     | 700               | 1.00          | 150                     | 5.2  | 47                    | C957B        |  |
| 1N958B | 7.125                           | 7.5 | 7.875 | 16.5         | 5.5                     | 700               | 0.50          | 75                      | 5.7  | 42                    | C958B        |  |
| 1N959B | 7.790                           | 8.2 | 8.610 | 15.0         | 6.5                     | 700               | 0.50          | 50                      | 6.2  | 38                    | C959B        |  |
| 1N960B | 8.645                           | 9.1 | 9.555 | 14.0         | 7.5                     | 700               | 0.50          | 25                      | 6.9  | 35                    | C960B        |  |
| 1N961B | 9.500                           | 10  | 10.50 | 12.5         | 8.5                     | 700               | 0.25          | 10                      | 7.6  | 32                    | C961B        |  |
| 1N962B | 10.45                           | 11  | 11.55 | 11.5         | 9.5                     | 700               | 0.25          | 5.0                     | 8.4  | 28                    | C962B        |  |
| 1N963B | 11.40                           | 12  | 12.60 | 10.5         | 11.5                    | 700               | 0.25          | 5.0                     | 9.1  | 26                    | C963B        |  |
| 1N964B | 12.35                           | 13  | 13.65 | 9.5          | 13.0                    | 700               | 0.25          | 5.0                     | 9.9  | 24                    | C964B        |  |
| 1N965B | 14.25                           | 15  | 15.75 | 8.5          | 16.0                    | 700               | 0.25          | 5.0                     | 11.4 | 21                    | C965B        |  |
| 1N966B | 15.20                           | 16  | 16.80 | 7.8          | 17.0                    | 700               | 0.25          | 5.0                     | 12.2 | 19                    | C966B        |  |
| 1N967B | 17.10                           | 18  | 18.90 | 7.0          | 21.0                    | 750               | 0.25          | 5.0                     | 13.7 | 17                    | C967B        |  |
| 1N968B | 19.00                           | 20  | 21.00 | 6.2          | 25.0                    | 750               | 0.25          | 5.0                     | 15.2 | 15                    | C968B        |  |
| 1N969B | 20.90                           | 22  | 23.10 | 5.6          | 29.0                    | 750               | 0.25          | 5.0                     | 16.7 | 14                    | C969B        |  |
| 1N970B | 22.80                           | 24  | 25.20 | 5.2          | 33.0                    | 750               | 0.25          | 5.0                     | 18.2 | 13                    | C970B        |  |
| 1N971B | 25.65                           | 27  | 28.35 | 4.6          | 41.0                    | 750               | 0.25          | 5.0                     | 20.6 | 11                    | C971B        |  |
| 1N972B | 28.50                           | 30  | 31.50 | 4.2          | 49.0                    | 1000              | 0.25          | 5.0                     | 22.8 | 10                    | C972B        |  |
| 1N973B | 31.35                           | 33  | 34.65 | 3.8          | 58.0                    | 1000              | 0.25          | 5.0                     | 25.1 | 9.2                   | C973B        |  |
| 1N974B | 34.20                           | 36  | 37.80 | 3.4          | 70.0                    | 1000              | 0.25          | 5.0                     | 27.4 | 8.5                   | C974B        |  |
| 1N975B | 37.05                           | 39  | 40.95 | 3.2          | 80.0                    | 1000              | 0.25          | 5.0                     | 29.7 | 7.8                   | C975B        |  |
| 1N976B | 40.85                           | 43  | 45.15 | 3.0          | 93.0                    | 1500              | 0.25          | 5.0                     | 32.7 | 7.0                   | C976B        |  |
| 1N977B | 44.65                           | 47  | 49.35 | 2.7          | 105                     | 1500              | 0.25          | 5.0                     | 35.8 | 6.4                   | C977B        |  |
| 1N978B | 48.45                           | 51  | 53.55 | 2.5          | 125                     | 2000              | 0.25          | 5.0                     | 38.8 | 5.9                   | C978B        |  |
| 1N979B | 53.20                           | 56  | 58.80 | 2.2          | 150                     | 2000              | 0.25          | 5.0                     | 42.6 | 5.4                   | C979B        |  |
| 1N980B | 58.90                           | 62  | 65.10 | 2.0          | 185                     | 2000              | 0.25          | 5.0                     | 47.1 | 4.9                   | C980B        |  |
| 1N981B | 64.60                           | 68  | 71.40 | 1.8          | 230                     | 2000              | 0.25          | 5.0                     | 51.7 | 4.5                   | C981B        |  |
| 1N982B | 71.25                           | 75  | 78.75 | 1.7          | 270                     | 2000              | 0.25          | 5.0                     | 56.0 | 4.0                   | C982B        |  |

R2 (6-December 2019)

1N957B THRU 1N992B


SILICON ZENER DIODE  
6.8 VOLTS THRU 200 VOLTS  
500mW, 5% TOLERANCE



ELECTRICAL CHARACTERISTICS - Continued: ( $T_A=25^\circ\text{C}$ )  $V_F=1.5\text{V MAX @ } I_F=200\text{mA}$  (for all types)

| TYPE   | ZENER VOLTAGE<br>$V_Z @ I_{ZT}$ |     |       | TEST CURRENT<br>$I_{ZT}$ | MAXIMUM ZENER IMPEDANCE |                   |      | MAXIMUM REVERSE CURRENT |       | MAXIMUM ZENER CURRENT<br>$I_{ZM}$ | MARKING CODE |
|--------|---------------------------------|-----|-------|--------------------------|-------------------------|-------------------|------|-------------------------|-------|-----------------------------------|--------------|
|        | MIN                             | NOM | MAX   |                          | $Z_{ZT} @ I_{ZT}$       | $Z_{ZK} @ I_{ZK}$ |      | $I_R @ V_R$             |       |                                   |              |
|        | V                               | V   | V     |                          | $\Omega$                | $\Omega$          | mA   | $\mu\text{A}$           | V     | mA                                |              |
| 1N983B | 77.90                           | 82  | 86.10 | 1.5                      | 330                     | 3000              | 0.25 | 5.0                     | 62.2  | 3.7                               | C983B        |
| 1N984B | 86.45                           | 91  | 95.55 | 1.4                      | 400                     | 3000              | 0.25 | 5.0                     | 69.2  | 3.3                               | C984B        |
| 1N985B | 95.00                           | 100 | 105.0 | 1.3                      | 500                     | 3000              | 0.25 | 5.0                     | 76.0  | 3.0                               | C985B        |
| 1N986B | 104.5                           | 110 | 115.5 | 1.1                      | 750                     | 4000              | 0.25 | 5.0                     | 83.6  | 2.7                               | C986B        |
| 1N987B | 114.0                           | 120 | 126.0 | 1.0                      | 900                     | 4500              | 0.25 | 5.0                     | 91.2  | 2.5                               | C987B        |
| 1N988B | 123.5                           | 130 | 136.5 | 0.95                     | 1100                    | 5000              | 0.25 | 5.0                     | 98.8  | 2.3                               | C988B        |
| 1N989B | 142.5                           | 150 | 157.5 | 0.85                     | 1500                    | 6000              | 0.25 | 5.0                     | 114.0 | 2.0                               | C989B        |
| 1N990B | 152.0                           | 160 | 168.0 | 0.80                     | 1700                    | 6500              | 0.25 | 5.0                     | 121.6 | 1.9                               | C990B        |
| 1N991B | 171.0                           | 180 | 189.0 | 0.68                     | 2200                    | 7100              | 0.25 | 5.0                     | 136.8 | 1.7                               | C991B        |
| 1N992B | 190.0                           | 200 | 210.0 | 0.65                     | 2500                    | 8000              | 0.25 | 5.0                     | 152.0 | 1.5                               | C992B        |

#### DO-35 CASE - MECHANICAL OUTLINE



| SYMBOL | DIMENSIONS |       |             |      |
|--------|------------|-------|-------------|------|
|        | INCHES     |       | MILLIMETERS |      |
|        | MIN        | MAX   | MIN         | MAX  |
| A      | 0.018      | 0.022 | 0.46        | 0.56 |
| B      | 0.120      | 0.200 | 3.05        | 5.08 |
| C      | 0.060      | 0.090 | 1.52        | 2.29 |
| D      | 1.000      | -     | 25.40       | -    |

DO-35 (REV: R1)







R2 (6-December 2019)

1N957B THRU 1N992B

SILICON ZENER DIODE  
6.8 VOLTS THRU 200 VOLTS  
500mW, 5% TOLERANCE



## ELECTRICAL CHARACTERISTICS



R2 (6-December 2019)

## OUTSTANDING SUPPORT AND SUPERIOR SERVICES



---

### PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

---

### DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

---

### REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

---

### CONTACT US

#### Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.  
145 Adams Avenue  
Hauppauge, NY 11788 USA  
Main Tel: (631) 435-1110  
Main Fax: (631) 435-1824  
Support Team Fax: (631) 435-3388  
[www.centrasemi.com](http://www.centrasemi.com)

**Worldwide Field Representatives:**  
[www.centrasemi.com/wwreps](http://www.centrasemi.com/wwreps)

**Worldwide Distributors:**  
[www.centrasemi.com/wwdistributors](http://www.centrasemi.com/wwdistributors)

---

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: [www.centrasemi.com/terms](http://www.centrasemi.com/terms)



<http://www.centrasemi.com>

## Product End of Life Notification

|                           |          |
|---------------------------|----------|
| <b>PDN ID:</b>            | PDN01046 |
| <b>Notification Date:</b> | 8/19/16  |
| <b>Last Buy Date:</b>     | 2/19/17  |
| <b>Last Shipment Date</b> | 8/19/17  |

Summary: The 1N979B through 1N992B, 0.5 watt Zener diodes in the DO-35 case, are discontinued and now classified as End of Life (EOL).

Although Central Semiconductor Corp. makes every effort to continue to produce devices that have been proclaimed EOL (End of Life) by various manufacturers, it is an accepted industry practice to discontinue certain devices when customer demand falls below a minimum level of sustainability. Accordingly, the following product(s) have been transitioned to End of Life status as part of Central's Product Management Process. Any replacement product will be noted below. The effective date for placing the last purchase order will be six(6) months from the date of this notice and twelve(12) months from the notice date for final shipments; this may be extended if inventory is available.

| <b>Central Part Number</b> | <b>Replacement</b> |
|----------------------------|--------------------|
| 1N979B BK                  | N/A                |
| 1N982B BK                  | N/A                |
| 1N984B BK                  | N/A                |
| 1N986B BK                  | N/A                |
| 1N987B BK                  | N/A                |
| 1N988B BK                  | N/A                |
| 1N988B TR                  | N/A                |
| 1N990B BK                  | N/A                |
| 1N991B BK                  | N/A                |
| 1N991B TR                  | N/A                |
| 1N992B BK                  | N/A                |

Central would be happy to assist you by providing additional information or technical data to help locate an alternate source if we have no replacement available. Please email your requests to [engineering@centrasemi.com](mailto:engineering@centrasemi.com).

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Central Semiconductor:

[1N963B TR](#) [1N958B BK](#) [1N964B BK](#) [1N971B BK](#) [1N963B BK](#) [1N973B BK](#) [1N961B BK](#) [1N959B BK](#) [1N966B TR](#)  
[1N957B TR](#) [1N972B TR](#) [1N961B TR](#) [1N969B TR](#) [1N968B BK](#) [1N970B BK](#) [1N974B BK](#) [1N975B TR](#) [1N969B BK](#)  
[1N975B BK](#) [1N972B BK](#) [1N965B BK](#) [1N962B BK](#) [1N971B TR](#) [1N957B BK](#) [1N964B TR](#) [1N959B TR](#) [1N973B TR](#)  
[1N960B BK](#) [1N970B TR](#) [1N978B BK](#) [1N978B TR](#) [1N965B TR TIN/LEAD](#) [1N960B TR TIN/LEAD](#) [1N974B BK](#)  
[TIN/LEAD](#) [1N972B TR TIN/LEAD](#) [1N975B BK TIN/LEAD](#) [1N978B TR TIN/LEAD](#) [1N973B BK TIN/LEAD](#) [1N970B BK](#)  
[TIN/LEAD](#) [1N971B TR TIN/LEAD](#) [1N978B BK TIN/LEAD](#) [1N962B BK TIN/LEAD](#) [1N959B BK TIN/LEAD](#) [1N959B TR](#)  
[TIN/LEAD](#) [1N972B BK TIN/LEAD](#) [1N973B TR TIN/LEAD](#) [1N962B TR TIN/LEAD](#) [1N961B BK TIN/LEAD](#) [1N957B BK](#)  
[TIN/LEAD](#) [1N975B TR TIN/LEAD](#) [1N967B BK TIN/LEAD](#) [1N964B BK TIN/LEAD](#) [1N964B TR TIN/LEAD](#) [1N971B BK](#)  
[TIN/LEAD](#) [1N966B TR TIN/LEAD](#) [1N967B TR TIN/LEAD](#) [1N960B BK TIN/LEAD](#) [1N969B TR TIN/LEAD](#) [1N958B BK](#)  
[TIN/LEAD](#) [1N970B TR TIN/LEAD](#) [1N963B BK TIN/LEAD](#) [1N963B TR TIN/LEAD](#) [1N961B TR TIN/LEAD](#) [1N968B BK](#)  
[TIN/LEAD](#) [1N965B BK TIN/LEAD](#) [1N969B BK TIN/LEAD](#) [1N958B TR TIN/LEAD](#) [1N957B TR TIN/LEAD](#)