




TOP VIEW



SIDE VIEW



BOTTOM VIEW



## Specifications

Description	Value	Unit
Directivity	Omnidirectional	
Technology	Electret Condenser	
Sensitivity	-44	(dB)
Frequency Range	100 ~ 10,000	(Hz)
Rated Voltage	2	(V)
Output Impedance	2,200	(Ohm)
Connection Method	Solder Pads	
Voltage Range	1.0 ~ 10.0	(V)
Max Rated Current	0.5	(mA)
Min. Signal to Noise Ratio	60	(dB)
Operating Temperature	-10 ~ +50	°C
Storage Temperature	-20 ~ +60	°C

## Notes

- 1) All dimensions are in mm unless otherwise noted  
 2) All parts meet RoHS



DB UNLIMITED

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			2/9/2014	J.S.
					</

Electret Condenser Microphone

MO044402-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[MO044402-1](#)