



Part Number:	TE122001-4	DRAWN CJ	2/15/2019
		CHECKED C.H.	2/18/2019
	Description: Electro-Mechanical Transducer	APPROVED C.E.	2/18/2019
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com			


Top View



Side View



Bottom View



Items	Specifications	Conditions	REVISION HISTORY			
Min. Sound Pressure Level	80	dB (@ 10cm)	REV	DESCRIPTION	DATE	APPROVED
Resonant Frequency	2,048	Hz		Released from Engineering	10/21/2013	J.S.
Rated Voltage	1.5	V	1	Updated drawing to new template, temps	2/18/2019	C.E.
Voltage Range	1 ~ 5	V				
Coil Resistance	50 ± 7.5	Ω				
Max. Rated Current	20	mA				
Storage Temperature	-40 ~ +85	°C				
Operating Temperature	-30 ~ +70	°C				
Connection Method	PC Pins					
Mount Type	Thru-Hole					
Housing Material	Noryl					
Weight	2	g				
			NOTES			
			1) All dimensions are in mm unless otherwise noted			
			2) All tolerances are ± 0.5 mm unless otherwise noted			
			3) All parts meet RoHS			
			4) Subject to change or redrawn without notice			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[TE122001-4](#)