

- Conduction cooled design approach
- Fanless operation with up to 90% output power
- Operating temperature range -30°C to +80°C
- I/O reinforced isolation 4250 VAC
- Over voltage category (OVC III)
- High efficiency up to 92%
- Operating up to 5000 m altitude
- Internal EN 55032 conducted class B filter
- Protection class I prepared
- 3-year product warranty



The TCI 500U is a 500 Watt conduction cooled AC/DC encased power supply series with a 4250 VAC reinforced isolation system. Traco Power's new TCI line focuses on maximizing the proficiency of conduction cooled systems as it offers superior temperature behavior when mounted on a metal chassis or baseplate. This way the TCI 500U can deliver up to 90% of the maximum output power without the need for a fan. Excellent efficiency of up to 92% allows the TCI series to operate from -30 to +50°C without derating, while going up to +80°C with either load derating or forced cooling. They also meet OVC III requirements and can operate at up to 5000 m altitude. Active power factor correction, EMC characteristics dedicated for applications in industrial/automation and test & measurement fields and high reliability make the new TCI line an ideal solution for any demanding industrial application.

Models

Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max. (Forced air cooling)	Output Current max. (Conduction Cooling)	Efficiency typ.
TCI 500-112U-T	500 W	12 VDC (11.4 - 12.6 VDC)	41'500 mA	37'500 mA	90 %
TCI 500-124U-T		24 VDC (22.8 - 25.2 VDC)	20'800 mA	18'750 mA	91 %
TCI 500-148U-T		48 VDC (45.6 - 50.4 VDC)	10'410 mA	9'375 mA	92 %

Options

TCI 500-AUX	- Optional Cable: www.tracopower.com/overview/tci500-aux
TCI-AC1	- Optional Cable: www.tracopower.com/overview/tci-ac1

Input Specifications

Input Voltage	- AC Range	Operational Range: 90 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
	- DC Range	Operational Range: 127 - 370 VDC (Designed for, no certification) Polarity: irrelevant
Input Frequency		Operational Range: 47 - 63 Hz Certified: 50/60 Hz
Power Consumption	- No load & Vin = 230 VAC	500 mW max. (Ready to meet ErP directive)
	- No load & Vin = 115 VAC	500 mW max.
Input Current	- Full load & Vin = 230 VAC	3'150 mA max.
	- Full load & Vin = 115 VAC	6'300 mA max.
Input Inrush Current	- At 230 VAC	80 A max.
	- At 115 VAC	40 A max.
Power Factor	- At 230 VAC	0.94 min. (Active Power Factor Correction)
	- At 115 VAC	0.94 min. (Active Power Factor Correction)
Input Protection		T 10 A / 250 VAC (Internal Fuse in L & N)
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		±5% (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±2% max.
Regulation	- Input Variation (Vmin - Vmax)	1% max.
	- Load Variation (10 - 100%)	1% max.
Ripple and Noise (20 MHz Bandwidth)	12 VDC model:	160 mVp-p max. (w/ 0.1 µF ceramic 47 µF KY)
	24 VDC model:	240 mVp-p max. (w/ 0.1 µF ceramic 47 µF KY)
	48 VDC model:	480 mVp-p max. (w/ 0.1 µF ceramic 47 µF KY)
Capacitive Load	12 VDC model:	5'000 µF max.
	24 VDC model:	2'500 µF max.
	48 VDC model:	1'250 µF max.
Minimum Load		1 % of Iout max. (Operation at lower load will not damage the converter, but it may not meet all specifications)
Temperature Coefficient		±0.06 %/K max. (-30°C - 0°C) ±0.03 %/K max. (0°C - 50°C)
Hold-up Time	- At 230 VAC	8 ms min.
	- At 115 VAC	8 ms min.
Start-up Time	- At 230 VAC	350 ms max.
	- At 115 VAC	350 ms max.
Short Circuit Protection		Continuous, Automatic recovery (Level 1, nom.) Latch (Level 2, instantaneous high current)
Output Current Limitation		113 - 161% of Iout max.
Overvoltage Protection		111 - 130% of Vout nom.
Transient Response	- Response Deviation	3% typ. / 5% max. (25% to 100% Load Step)
	- Response Time	2'000 µs typ. / 3'000 µs max. (25% to 100% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/tci500u
Protection Class		Class I (Prepared): Connection to PE

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Pollution Degree	PD 2
Over Voltage Category	OVC II OVC III

EMC Specifications

EMI (Emissions)	- Conducted Emissions - Radiated Emissions - Harmonic Current Emissions	EN 55032 class B (internal filter) EN 55032 class A (internal filter) EN 61000-3-2, class A
EMS (Immunity)	- Electrostatic Discharge - RF Electromagnetic Field - EFT (Burst) / Surge - Conducted RF Disturbances - PF Magnetic Field - Voltage Dips & Interruptions	EN 55035 (Multimedia) Air: EN 61000-4-2, ± 8 kV, perf. criteria A Contact: EN 61000-4-2, ± 4 kV, perf. criteria A EN 61000-4-3, 3 V/m, perf. criteria A EN 61000-4-4, ± 1 kV, perf. criteria A L to L: EN 61000-4-5, ± 1 kV, perf. criteria A L to PE: EN 61000-4-5, ± 2 kV, perf. criteria A EN 61000-4-6, 3 Vrms, perf. criteria A Continuous: EN 61000-4-8, 1 A/m, perf. criteria A 230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 250 periods, perf. criteria B 115 VAC / 60 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 250 periods, perf. criteria B
EMC / Environmental	- Certification Documents	www.tracopower.com/overview/tci500u

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Storage Temperature	-30°C to +80°C -30°C to +85°C
Power Derating	- High Temperature - Low Input Voltage	Depending on model 3 %/V below 100 VAC See application note: www.tracopower.com/overview/tci500u
Over Temperature Protection Switch Off	- Protection Mode - Measurement Point	115°C min. / 120°C typ. / 125°C max. (Automatic recovery at 90°C typ.) Internal IC temperature
Cooling System		Forced air cooling (with external fan, 30 CFM) Conduction Cooling (with a 450 x 450 x 3.0 mm aluminum plate) Natural Convection (20 LFM)
Fan Power Source	- Output Voltage - Output Current	12 VDC 209 mA max. (Fan output voltage: 10.2 - 13.3 VDC when output load > 3% and fan current > 0.1 mA)
Standby Power Source	- Output Voltage - Output Current	5 VDC 400 mA max. (1 A max. (with forced air cooling))
Remote Control	- Voltage Controlled Remote (passive = on) - Off Idle Input Current - Remote Pin Input Current	On: 3.3 to 5 VDC or open circuit Off: 0 to 1.0 VDC or short circuit Refers to '+Remote' and '-Remote' Pin 92 mA typ. / 155 mA max. 8 to 30 mA
Altitude During Operation		4'000 m max. (for OVC III) 5'000 m max. (for OVC II)
Regulator Topology		LCC Converter
Switching Frequency		58 - 76 kHz (PFM) 67 kHz typ. (PFM)

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Insulation System	Reinforced Insulation
Working Voltage (rated)	277 VAC
Isolation Test Voltage	- Input to Output, 60 s - Input to Case or PE, 60 s - Output to Case or PE, 60 s
	4'250 VAC (6'000 VDC) 2'830 VAC (4'000 VDC) 1'500 VAC (2'121 VDC)
Isolation Resistance	- Input to Output, 500 VDC
	100 MΩ min.
Leakage Current (at 264 VAC / 63 Hz)	- Earth Leakage Current
	1500 μA max.
Distance Through Isolation	7.1 mm
Reliability	- Calculated MTBF
	160'000 h (MIL-HDBK-217F, ground benign)
Washing Process	Not allowed
Environment	- Vibration
	IEC 60068-2-6 2 g, 3 axis, 60 min, 10-500 Hz, 10 min/cycle
	- Mechanical Shock
	IEC 60068-2-27 50 g, 3 axis, half sine, 11 ms
Housing Material	Aluminum
Potting Material	Silicone (UL 94 V-0 rated) (the converter is partly potted on the bottom)
Housing Type	Metal Case
Mounting Type	Chassis Mount
Connection Type	Screw Terminal, Pin Connector
Weight	710 g
Power OK Signal	Voltage source output
	High level
	Low level
	(Refers to 'PG' and 'GND' Pin)
Status Indicator	Indicated by green LED
Sense Function	3% max. of Vout nom.
Environmental Compliance	- REACH Declaration
	www.tracopower.com/info/reach-declaration.pdf
	REACH SVHC list compliant
	REACH Annex XVII compliant
	www.tracopower.com/info/rohs-declaration.pdf
	Exemptions: 7a, 7c-I
	(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)
	- SCIP Reference Number
	47ec4091-32e0-4625-9fc8-8d2dcbfddbcd


Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tci500u

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Input	
Pin	Function
1	AC (N)
2	No Pin
3	AC (L)

Output	
Pin	Function
4	+Vout
5	-Vout**

Auxiliary	
CN1	
Pin	Function
1	-Standby**
2	+Standby
3	GND
4	Power Good
5	-Remote**
6	+Remote
7	-Sense**
8	+Sense

FAN	
Pin	Function
1	+12V
2	GND

Case	
(no dedicated connector)	
Pos	Function
A	For mounting on chassis only
B	For mounting on PCB or chassis, and connecting PE
C	For connecting PE only

Input: JST series
mates with JST crimp terminal: SVH-41T-P1.1 or Equivalent
and terminal housing: VHR-3N or Equivalent

Output: Screw Terminal
M3.5 Pozzi Pan Head Screw
max. torque: 0.9 Nm (9.1 kgfcm)

Auxiliary: JST series
mates with JST crimp terminal: SPHD-001T-P0.5 or Equivalent
and terminal housing: PHDR-08VS or Equivalent

FAN: JST series
mates with JST crimp terminal: SXH-002T-P0.6 or Equivalent
and terminal housing: XHP-2 or Equivalent

**Internally connected with GND

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TRACO Power:](#)

[TCI 500-112U-T](#) [TCI 500-124U-T](#) [TCI 500-148U-T](#)