


- Ultra compact 15 Watt converter in DIP-16 metal casing
- Highest power density of 4.51 W/cm³
- Operating temperature range -40°C to +85°C
- Wide 4:1 input voltage ranges: 9-36, 18-75 VDC
- High efficiency (up to 87%) for low thermal loss
- 6-side shielded metal case with insulated baseplate
- Built-In EN 55032 class A filter (conducted)
- Protection against short circuit
- 3-year product warranty



The TEL 15WIN is a series of isolated 15 Watt converters which come in an ultra compact DIP-16 metal package. The design purpose of this series was to miniaturized low power DC/DC converters to the maximum without sacrificing high efficiency. It solidifies the new standard for power density with 4.51 W/cm³ and effectively doubles the power density compared to 15 Watt converters in DIP-24 packages. The TEL 15WIN offers a wide 4:1 input voltage range and features a high efficiency of up to 87% which enables an operation temperature of up to +55°C at full load and up to 85°C with 50% load. The converters also have an internal input filter to comply with conducted emission standard EN 55032 class A. It's an economical solution for space critical and cost sensitive applications in instrumentation, IT and industrial electronics.

Models						
Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
TEL 15-2411WIN	9 - 36 VDC (24 VDC nom.)	5.1 VDC	2'940 mA			86 %
TEL 15-2412WIN		12 VDC	1'250 mA			87 %
TEL 15-2413WIN		15 VDC	1'000 mA			87 %
TEL 15-2415WIN		24 VDC	625 mA			87 %
TEL 15-2422WIN		+12 VDC	625 mA	-12 VDC	-625 mA	87 %
TEL 15-2423WIN		+15 VDC	500 mA	-15 VDC	-500 mA	87 %
TEL 15-4811WIN	18 - 75 VDC (48 VDC nom.)	5.1 VDC	2'940 mA			86 %
TEL 15-4812WIN		12 VDC	1'250 mA			87 %
TEL 15-4813WIN		15 VDC	1'000 mA			87 %
TEL 15-4815WIN		24 VDC	625 mA			87 %
TEL 15-4822WIN		+12 VDC	625 mA	-12 VDC	-625 mA	87 %
TEL 15-4823WIN		+15 VDC	500 mA	-15 VDC	-500 mA	87 %

Note - 48 Vin models: If the input will be switched electromechanically, use an external 27 µF / 200 V / KXY capacitor to reduce voltage transient.

Input Specifications

Input Current	- At no load	24 Vin models: 10 mA typ. 48 Vin models: 7 mA typ.
	- At full load	24 Vin models: 720 mA typ. 48 Vin models: 360 mA typ.
Surge Voltage		24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Input Inrush Current		36.6 A typ. (24 Vin models) 34.2 A typ. (48 Vin models)
Under Voltage Lockout		24 Vin models: 8 VDC typ. 48 Vin models: 16 VDC typ.
Recommended Input Fuse		24 Vin models: 3'000 mA (slow blow) 48 Vin models: 1'500 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications

Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.8% max. dual output models: 0.8% max.
	- Load Variation (0 - 100%)	single output models: 1% max. dual output models: 1% max. (Output 1) 1% max. (Output 2)
	- Voltage Balance (symmetrical load)	dual output models: 2% max.
	- Cross Regulation (25% / 100% asym. load)	dual output models: 5% max.
	- 20 MHz Bandwidth	70 mVp-p typ. (w/ 2.2 µF / 50 V MLCC)
Capacitive Load	- single output	5.1 Vout models: 1'800 µF max. 12 Vout models: 820 µF max. 15 Vout models: 820 µF max. 24 Vout models: 270 µF max.
	- dual output	12 / -12 Vout models: 560 / 560 µF max. 15 / -15 Vout models: 270 / 270 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Start-up Time		40 ms max.
Short Circuit Protection		Continuous, Automatic recovery (Hiccup Mode, Automatic Recovery)
Output Current Limitation		110% min. of Iout max. 160% typ. of Iout max.
Transient Response	- Response Deviation	3% typ. / 5% max. (75% to 100% Load Step)
	- Response Time	500 µs max. (75% to 100% Load Step)

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/tel15win
Pollution Degree		PD 3
Over Voltage Category		Not mains connected

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class A (internal filter)
	- Radiated Emissions	EN 55032 class B (with external filter)
External filter proposal:		EN 55032 class A (with external filter)
		EN 55032 class B (with external filter)
		www.tracopower.com/overview/tel15win
EMS (Immunity)	- Electrostatic Discharge	EN 55024 (IT Equipment)
		EN 55035 (Multimedia)
	- RF Electromagnetic Field	Air: EN 61000-4-2, ± 8 kV, perf. criteria A
		Contact: EN 61000-4-2, ± 6 kV, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-3, 20 V/m, perf. criteria A
		EN 61000-4-4, ± 2 kV, perf. criteria A
	- Conducted RF Disturbances	EN 61000-4-5, ± 2 kV, perf. criteria A
		External filter proposal: www.tracopower.com/overview/tel15win
EMC / Environmental	- PF Magnetic Field	EN 61000-4-6, 10 Vrms, perf. criteria A
		Continuous: EN 61000-4-8, 30 A/m, perf. criteria A
	- Certification Documents	www.tracopower.com/overview/tel15win

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +80°C
	- Case Temperature	+110°C max.
	- Storage Temperature	-50°C to +125°C
Power Derating	- High Temperature	1.9 %/K above 55°C (average)
		See application note: www.tracopower.com/overview/tel15win
Cooling System		Natural convection (20 LFM)
Altitude During Operation		6'000 m max.
Regulator Topology		Flyback Converter
Switching Frequency		420 - 540 kHz (PWM)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'500 VDC
	- Input to Output, 1 s	1'800 VDC
	- Input to Case, 60 s	1'000 VDC
	- Output to Case, 60 s	1'000 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	2'200 pF max.
Reliability	- Calculated MTBF	2'000'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Environment	- Vibration	2.4 g, 3 axis, random waveform, 30 min
	- Mechanical Shock	30 g, 3 axis, half sine, 11 ms
	- Thermal Shock	IPC-9592B
Housing Material		Aluminum
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper Alloy (C6801)
Pin Foundation Plating		Nickel (2 - 4 μm)
Pin Surface Plating		Tin (3 - 5 μm), matte
Housing Type		Metal Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		DIP16
Soldering Profile		Lead-Free Wave Soldering
		260°C / 10 s max.
Weight		8.8 g
Thermal Impedance	- Case to Ambient	24.6 K/W typ.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 7a

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)

- SCIP Reference Number


9ffe0ce5-4f97-4cce-bcb9-8cf28bbf9e24

Supporting Documents

[Overview Link](#) (for additional Documents)

www.tracopower.com/overview/tel15win

Outline Dimensions



Dimensions in mm (inch)

Tolerances: X.X ± 0.5 (X.XX ± 0.02)

X.XX ± 0.25 (X.XXX ± 0.01)

Pin diameter tolerances: X.X ± 0.05 (X.XX ± 0.002)

Pinout

Pin	Single	Dual
1	-Vin	
8	NC	Common
9	+Vout	
10	-Vout	
16	+Vin	

NC: Not connected

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TRACO Power:](#)

[TEL 15-2411WIN](#) [TEL 15-2412WIN](#) [TEL 15-2413WIN](#) [TEL 15-2415WIN](#) [TEL 15-2422WIN](#) [TEL 15-2423WIN](#) [TEL 15-4811WIN](#) [TEL 15-4812WIN](#) [TEL 15-4813WIN](#) [TEL 15-4815WIN](#) [TEL 15-4822WIN](#) [TEL 15-4823WIN](#)