

Features

- ◆ Very compact power modules with screw terminal connection
- ◆ Active PFC, power factor >0.95 (230VAC), >0.99 (115 VAC)
- ◆ High efficiency up to 93% typ.
- ◆ Remote On/Off input
- ◆ Adjustable output voltage ±5%
- ◆ LED output indicator
- ◆ Universal input 100-240 VAC nominal
- ◆ Low leakage current
- ◆ EMI meets EN 55032, class B
- ◆ Protection class II prepared



The TML 100C series modules are very compact 85–100 Watt power supplies in a fully encapsulated plastic case. Active power factor correction and high efficiency across full load range qualify these modules for installation in energy related products. They feature screw terminals for easy installation. The TML 100C series is accompanied by an international safety approval package for worldwide markets.

Models

Order code	Output power max.	Output voltage	Output current max.	Efficiency
TML 100-112C	85	12 VDC	7080 mA	90 %
TML 100-115C	85	15 VDC	5660 mA	90 %
TML 100-124C	100	24 VDC	4200 mA	92 %
TML 100-148C	100	48 VDC	2100 mA	93 %

Full TML and TMLM Series Model Range

Series	Description	Datasheet
TMLM 04	4 Watt, PCB mount, single and dual output models	www.tracopower.com/products/tmlm.pdf
TMLM 05	5 Watt, PCB mount, single output models	
TMLM 10	10 Watt, PCB mount, single output models	
TMLM 20	20 Watt, PCB mount, single output models (compact design)	
TML 20	20 Watt, PCB & chassis mount, single, dual and triple output models	www.tracopower.com/products/tml.pdf
TML 40	40 Watt, PCB & chassis mount, single, dual and triple output models	

Input Specifications

Input voltage ranges	– nominal – AC full range – DC Input	100 – 240 VAC (universal input) 90 – 264 VAC 120 – 370 VDC
Input frequency		47 – 63 Hz
Input current at full load (115 VAC / 230 VAC nominal input)		< 2.0 A / < 1.0 A max.
Leakage current		0.5 mA max.
Harmonic limits	– Power factor	EN 61000-3-2, Class A >0.99 at 115 VAC, >0.95 at 230 VAC

Output Specifications

Voltage set accuracy		±2 %
Output voltage adjustment range		±5% (see page 3)
Minimum load		3% of rated max current (operation at lower load condition is safe but a higher output ripple will be experienced)
Ripple and noise (20 MHz bandwidth)	12 VDC model: 15 VDC model: 24 VDC model: 48 VDC model:	120 mV max. 150 mV max. 200 mV max. 240 mV max.
Regulation	– input variation – load variation	±1% ±1%
Current limitation		105% – 180% of rated output power. (automatic recovery)
Overvoltage protection		by Zener diode
Short circuit protection		indefinite (hiccup, automatic recovery)
Hold-up time		10 ms min. (110VAC)
Max. capacitive load	12 VDC model: 15 VDC model: 24 VDC model: 48 VDC model:	50'000 µF 40'000 µF 6'000 µF 560 µF

General Specifications

Temperature ranges	– Operating – Power derating above +50°C – Case max. – Storage (non operating)	–25°C to +70°C 3.75 %/K +95°C –25°C to +85°C
Temperature coefficient		0.03 %/K
Efficiency		see model table
Remote On/Off control		On: open or connection to -Vout Off: external +5VDC
Humidity (non condensing)		95 % rel max.
Altitude during operation		2'000 m max.
Switching frequency (pulse width modulation PWM)		100–133 kHz
Isolation voltage	– Input/Output	3'000 VAC
Working voltage (rated)		286 VAC
Reliability /calculated MTBF (MIL-HDBK-217F, at +25°C, ground benign)		>250'000 h
Environmental compliance	– Reach – RoHS	www.tracopower.com/info/reach-declaration.pdf RoHS directive 2011/65/EU

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

General Specifications

Electromagnetic compatibility (EMC), Emissions

EN 61000-3-2:2006+A1:2009+A2:2009
 EN 61000-3-3:2008
 EN 55032 class B (internal filter)

Electromagnetic compatibility (EMC), Immunity

- Electrostatic discharge ESD (air/contact)
- RF field susceptibility
- Electrical fast transient / burst immunity input
- Surge immunity line – neutral
- Surge immunity line – PE, neutral – PE
- Immunity to conducted RF disturbances
- Power frequency magnetic field immunity
- Mains voltage dips and interruptions

EN 55024 (IT Equipment)
 EN 55035 (Multimedia)
 EN 61000-4-2 ± 2 kV / ± 4 kV, criteria A
 EN 61000-4-3 3 V/m, criteria A
 EN 61000-4-4 ± 1 kV, criteria A
 EN 61000-4-5, ± 1 kV, criteria A
 EN 61000-4-5 ± 2 kV, criteria A
 EN 61000-4-6 3 V, criteria A
 EN 61000-4-8 1 A/m, criteria A
 EN 61000-4-11 30 % 500 ms, criteria A
 95 % 10 ms, criteria A
 95 % 2500 ms, criteria C

Protection class

class I and class II prepared

Safety standards

IEC/EN 60950-1, UL 60950-1
 IEC/EN 62368-1, UL 62368-1

Safety approvals

– Certification documents

www.tracopower.com/overview/tml100c

Casing material

plastic resin + fiberglass (UL 94V-0 rated)




Output voltage adjustment (Trim resistor [KOhm])

Trim up: Resistor from Trim to -Vout (connection 7-6)

Trim down: Resistor from Trim to +Vout (connection 7-5)

output voltage	12 VDC	15 VDC	24 VDC	48 VDC
+5%	85	95	90	85
nominal	open	open	open	open
-5%	220	300	600	1500

Outline Dimensions



Weight : 440 g (15.5 oz)

Connection

con.	Output
1	AC in (L)
2	AC in (N)
3	FG
4	Remote On/Off
5	+Vout
6	-Vout
7	Trim

Terminal screw locked torque:
 0.29 Nm (3 kgcm)

All dimensions in mm (inch)
 Tolerances: 0.5 (0.02)
 Mounting screw locked torque: 3 Nm (0.29 kgcm)

Specifications can be changed without notice! Make sure you are using the latest documentation, downloadable at www.tracopower.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TRACO Power:](#)

[TML 100-148C](#) [TML 100-124C](#) [TML 100-112C](#) [TML 100-115C](#)