

- Highest power density in SIP-8 metal package (optional plastic package)
- Ultra wide 4:1 input voltage range
- Temperature range -40° to $+85^{\circ}\text{C}$
- High efficiency up to 89%
- Indefinite short-circuit protection
- I/O isolation 1'600 VDC
- Remote On/Off control
- Fully RoHS compliant
- 3-year product warranty



The TMR 9WI series is a new family of isolated 9W DC/DC converter modules with regulated output, featuring ultra wide 4:1 input voltage ranges. The product comes in a ultra-compact SIP-8 metal package with a small footprint occupying only 2.0 cm² (0.3 square inch) of board space. An excellent efficiency allows -40° to $+60^{\circ}\text{C}$ operation temperatures without derating. Further features include remote On/Off control and continuous short circuit protection. The very compact dimensions of these converters make them an ideal solution for many space critical applications in communication equipment, instrumentation and industrial electronics.

Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
TMR 9-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2'000 mA			82 %
TMR 9-2411WI		5 VDC	1'600 mA			85 %
TMR 9-2419WI		9 VDC	1'000 mA			88 %
TMR 9-2412WI		12 VDC	750 mA			88 %
TMR 9-2413WI		15 VDC	600 mA			89 %
TMR 9-2415WI		24 VDC	375 mA			89 %
TMR 9-2421WI		+5 VDC	800 mA	-5 VDC	800 mA	86 %
TMR 9-2422WI		+12 VDC	375 mA	-12 VDC	375 mA	88 %
TMR 9-2423WI		+15 VDC	300 mA	-15 VDC	300 mA	88 %
TMR 9-4810WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	2'000 mA			82 %
TMR 9-4811WI		5 VDC	1'600 mA			85 %
TMR 9-4819WI		9 VDC	1'000 mA			89 %
TMR 9-4812WI		12 VDC	750 mA			89 %
TMR 9-4813WI		15 VDC	600 mA			89 %
TMR 9-4815WI		24 VDC	375 mA			89 %
TMR 9-4821WI		+5 VDC	800 mA	-5 VDC	800 mA	85 %
TMR 9-4822WI		+12 VDC	375 mA	-12 VDC	375 mA	88 %
TMR 9-4823WI		+15 VDC	300 mA	-15 VDC	300 mA	87 %

Options

on demand (backorder with MOQ non stocking item)	- models with plastic case
--	----------------------------

Input Specifications

Input Current	- At no load	24 Vin models: 7 mA typ. 48 Vin models: 3 mA typ.
Surge Voltage		24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Recommended Input Fuse		24 Vin models: 3'150 mA (slow blow) 48 Vin models: 1'250 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Capacitor

Output Specifications

Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.2% max. dual output models: 0.2% max.
	- Load Variation (0 - 100%)	single output models: 1% max. dual output models: 1% max. (Output 1) 1% max. (Output 2)
	- Cross Regulation (25% / 100% asym. load)	dual output models: 5% max.
Ripple and Noise (20 MHz Bandwidth)	- single output	3.3 Vout models: 50 mVp-p typ. (w/ 1 µF X7R) 5 Vout models: 50 mVp-p typ. (w/ 1 µF X7R) 9 Vout models: 50 mVp-p typ. (w/ 1 µF X7R) 12 Vout models: 75 mVp-p typ. (w/ 1 µF X7R) 15 Vout models: 75 mVp-p typ. (w/ 1 µF X7R) 24 Vout models: 75 mVp-p typ. (w/ 1 µF X7R)
	- dual output	5 / -5 Vout models: 50 / 50 mVp-p typ. (w/ 1 µF X7R) 12 / -12 Vout models: 75 / 75 mVp-p typ. (w/ 1 µF X7R) 15 / -15 Vout models: 75 / 75 mVp-p typ. (w/ 1 µF X7R)
Capacitive Load	- single output	3.3 Vout models: 2'600 µF max. 5 Vout models: 1'300 µF max. 9 Vout models: 800 µF max. 12 Vout models: 560 µF max. 15 Vout models: 560 µF max. 24 Vout models: 200 µF max.
	- dual output	5 / -5 Vout models: 800 / 800 µF max. 12 / -12 Vout models: 390 / 390 µF max. 15 / -15 Vout models: 200 / 200 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Start-up Time		50 ms typ.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		180% typ. of Iout max.
Transient Response	- Response Time	250 µs typ. (25% Load Step)

Safety Specifications

Safety Standards	- IT / Multimedia Equipment	EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1
	- Certification Documents	www.tracopower.com/overview/tmr9wi
Pollution Degree		PD 2

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

EMC Specifications

EMI Emissions	- Conducted Emissions	EN 55032 class A (with external filter)
	- Radiated Emissions	EN 55032 class B (with external filter)
External filter proposal:		www.tracopower.com/overview/tmr9wi
EMS Immunity	- Electrostatic Discharge	Air: EN 61000-4-2, ± 8 kV, perf. criteria A
	- RF Electromagnetic Field	Contact: EN 61000-4-2, ± 6 kV, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-3, 20 V/m, perf. criteria A
		EN 61000-4-4, ± 2 kV, perf. criteria A
		EN 61000-4-5, ± 2 kV, perf. criteria A
	- Conducted RF Disturbances	Ext. input component: 24 Vin models: KY 220 μ F // SMDJ70A
	- PF Magnetic Field	48 Vin models: KY 220 μ F // SMDJ120A
		Continuous: EN 61000-4-6, 10 Vrms, perf. criteria A
		EN 61000-4-8, 100 A/m, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +85°C
	- Case Temperature	+105°C max.
	- Storage Temperature	-55°C to +125°C
Power Derating	- High Temperature	See application note: www.tracopower.com/overview/tmr9wi
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote	On: 0 to 0.5 VDC or open circuit
	- Off Idle Input Current	Off: 3 to 12 VDC Refers to 'Remote' and '-Vin' Pin 2.5 mA max.
Altitude During Operation		2'000 m max. (for basic insulation)
		5'000 m max. (for functional insulation)
Switching Frequency		400 kHz typ. (PWM) (single output models) 500 kHz typ. (PWM) (dual output models)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'600 VDC
	- Input to Case, 60 s	1'000 VDC
	- Output to Case, 60 s	1'000 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 M Ω min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	50 pF max.
Reliability	- Calculated MTBF	2'940'000 h (for standard version)
		2'640'000 h (for plastic version)
		(MIL-HDBK-217F, ground benign)
Environment	- Vibration	MIL-STD-810F
	- Thermal Shock	MIL-STD-810F
Housing Material		Copper (for standard version) non-conductive plastic (for plastic version)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Copper
Pin Foundation Plating		Nickel (2 - 3 μ m)
Pin Surface Plating		Tin (3 - 5 μ m), matte
Connection Type		THD (Through-Hole Device)
Weight		5.9 g (for standard version)
		4.8 g (for plastic version)

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

- RoHS Declaration

Exemptions: 7a, 7c-I

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).
The SCIP number is provided on request.)


Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tmr9wi


Outline Dimensions

Metal package (standard)



Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout
9	Case	Case
10	Stand Off	Stand Off
11	Stand Off	Stand Off
12	Case	Case

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

Plastic package (option)


Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TRACO Power:

[TMR 9-4815WI](#) [TMR 9-4822WI](#) [TMR 9-2411WI](#) [TMR 9-2412WI](#) [TMR 9-2422WI](#) [TMR 9-2421WI](#) [TMR 9-2413WI](#)
[TMR 9-2410WI](#) [TMR 9-2415WI](#) [TMR 9-4811WI](#) [TMR 9-4821WI](#) [TMR 9-4819WI](#) [TMR 9-2419WI](#) [TMR 9-4810WI](#)
[TMR 9-4812WI](#) [TMR 9-2423WI](#) [TMR 9-4813WI](#) [TMR 9-4823WI](#)