

UPD78F1504AGC-UEU-AX

 User's Manual: Hardware

Overview

Design Support

Documentation

Sample Code

Software & Tools

Ordering

PARAMETRICS

Parameters	UPD78F1504AGC-UEU-AX
Package	
Pin Count	100
Package Type	LFQFP
Memory	
Program memory	96 KB Flash memory
RAM	6 KB
CPU (Bit, Clock, DMA, External Bus etc)	
CPU	78K0R (16-bit)
Max. Frequency	20 MHz
Sub-Clock (32.768 kHz)	YES
On-chip Oscillator Freq.	20, 8, 1 MHz
Power-On Reset	YES
Low Voltage Detection	YES
DMA Remarks	DMAC x 2 ch
External Interrupt Pins	12
I/O Ports	65
Timers	
16-bit Timers	12 ch
Watchdog Timers	1 ch
PWM Output	7
Analog	
A/D Converters	12-bit x 12 ch
D/A Converters	12-bit x 2 ch
Interfaces	
CSIs	3 ch
UARTs	4 ch
I2Cs	3 ch
LIN	1 ch
Display Functions	
LCD Remarks	seg=36, com=8
Operating Conditions	
Operating Voltage	1.8 to 5.5 V
Operating Temperature	-40 to 85 °C (Ambient Temperature)
Remarks	
Remarks	100-pin 16-bit single-chip microcontroller (78K0R/LG3)

 [View Less](#)

Need More Help?

- Contact Us

Forums

Knowledgebase
- Website Feedback

Videos

About Renesas

- News

Investors

Careers

Follow Us

-  Facebook

 YouTube
-  Twitter

 LinkedIn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renesas Electronics:](#)

[UPD78F1504AGC-UEU-AX](#)