

**Elektrodynamischer Exciter** zur Anregung von Platten zu BiegeWellenschwingungen. Die Befestigung des Exciters auf der Oberfläche der anzuregenden Platte kann durch Kleben oder Schrauben erfolgen.

**Anwendungsmöglichkeiten:** Signalausgabe in Anwendungen aller Art, bei denen aus Designgründen oder zum Schutz vor Umwelteinflüssen oder Vandalismus keine sichtbaren Lautsprecher verbaut werden können.

**Eigenschaften:**

- erfüllt Anforderungen der EN 60068-2-14 (Temperaturwechsel, zyklisch: -40 °C/+80 °C)
- erfüllt Anforderungen der EN 61373 (Schwingen, Schocken: Kategorie 1/Klasse B)

**Zubehör:** Pad EX 60 S (Art. No. 4556)


**Electro dynamical exciter** for stimulating bending waves on plates. The unit can be attached to the surface of the plate by gluing or screwing.

**Typical applications:** Signal output in every application where normal speakers can not be installed for optical reasons or for protection against environment conditions or vandalism.

**Attributes:**


- Complies with standard EN 60068-2-14 (change of temperature, cyclic: -40 °C/+80 °C)
- Complies with standard EN 61373 (vibration, shock: category 1/class B)

**Accessories:** Pad EX 60 S (Art. No. 4556)



**KlebePad** zur Befestigung des Exciters EX 60 S auf glatten Oberflächen.  
Typ: 3M VHB 4919F

**Gluing pad** for fitting the EX 60 S exciters on flat surfaces.  
Type: 3M VHB 4919F



Pad EX 60 S  
04.09.2017

**EX 60 S**

Art. No. 4536 – 4 Ω

Art. No. 4506 – 8 Ω



**Technische Daten / Technical Data**

|                          |                                   |
|--------------------------|-----------------------------------|
| Belastbarkeit            |                                   |
| Power                    | 25 W *)                           |
| Impedanz                 |                                   |
| Impedance                | 4 Ω / 8 Ω                         |
| Schwingspulendurchmesser |                                   |
| Voice coil diameter      | 32,5 mm Ø                         |
| Anschluss                |                                   |
| Terminal                 | 4,8 x 0,8 mm (+)/2,8 x 0,8 mm (-) |
| Gewicht netto            |                                   |
| Net weight               | 0,12 kg                           |

\*) Maximale Langzeitleistung nach DIN EN 60268-5  
Maximum long-term power according to DIN EN 60268-5

**Pad EX 60 S**

Art. No. 4556



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Visaton:

[EX 60 S - 4 ohm](#)