

CT2887

MicroLead, 0.031 Jack to 4mm Jack

Individual lead 08mm female jack to 4mm banana jack

Description

Individual lead for interconnecting MicroClip Test Clips and MiniFlex Clips to instrument. 0.8mm female jack to 4mm banana jack with Silicone lead wire. Connect a MicroClip Test Clip to a sheathed banana plug lead for DMM use.

- Highly flexible Silicone lead wire
- Material: Brass, Gold Plt.
- Available in black and red as a pair



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

| | |
|------------------------------|----------------------|
| IEC Rating | 33 Vac / 70 Vdc |
| Current Max | 2 A |
| Resistance Max | 8 milliohms |
| Jacket Material | Silicone |
| Conductor Area | 0.22 mm ² |
| Wire Gauge | 24 AWG |
| Stranding | 7 x 0.20 mm |
| OD | 1.4mm (0.055") |
| Temperature (degrees) | -20 to +80 C |
| RoHS (2011/65/EU) | Compliant |

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2887-10-2](#) [CT2887-10-0](#)