

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.


REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	10/13/03	


- SAFETY JACK, REAR MOUNT, VERTICAL PCB, LONG PIN.
- SPECIFICATIONS:
INSULATOR: POLYACETAL
CONTACT: BRASS, NICKEL PLATED
- RATING:
VOLTAGE: 1,000 V CATIII P2 (IEC 61010-031)
CURRENT: 25A MAX.
RESISTANCE: <5mΩ.
TEMPERATURE: -20° C TO +80° C.
- MOUNTING: REF. DIAGRAM
- MAXIMUM PANEL THICKNESS: .12 (3).

PART NUMBER

CT3150-#

COLOR: 0 - BLACK
1 - BROWN
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
7 - PURPLE
8 - GRAY
9 - WHITE



THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ±.005 DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610						
			APPROVALS		DATE		TITLE 4mm SAFETY JACK, VERTICAL PCB MOUNT, LONG PIN				
			DRAWN WDH		10/13/03						
			CHECKED								
			ENGR.								
MATERIAL		DESIGN ACTIVITY		SIZE A		CAGE CODE 43F45		DWG. NO. P315000		REV. —	
FINISH						SCALE 1:1				SHEET 1 OF 1	
NEXT ASSY		USED ON									
APPLICATION											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3150-0](#) [CT3150-2](#) [CT3150-9](#) [CT3150-6](#) [CT3150-5](#) [CT3150-4](#)