

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

## NOTES:

- 4mm SHEATHED (SAFETY) JACK, REAR MOUNT, HORIZONTAL & VERTICAL PCB.
- SPECIFICATIONS:
  - INSULATOR: POLYAMIDE PA 66 (NYLON):
    - BASF ULTRAMID, ASK RO1, V-2, UL QMFZ2.
    - TEKNOR APEX CHEMLON 104 H, HB.
  - CONTACT: BRASS, COPPER ALLOY C26800, H02, NICKEL PLATED, 1-3 MICROMETERS.
- RATING:
  - VOLTAGE: 1,000 V CAT III, P2.
  - CURRENT: 25 A MAX.
  - RESISTANCE: <5 mΩ
  - TEMPERATURE: -20°C TO +65°C MAX.
- MOUNTING: REF. DIAGRAMS.
- MAXIMUM PANEL THICKNESS: 3mm (0.12")
- MODEL CT3151xx-#, UL RECOGNIZED COMPONENT, CCN: PICQ2, PICQ8 FILE NUMBER: E315929.
- MODELS ARE RoHS 2 COMPLIANT.
- STANDARDS: UL 61010-1; CAN/CSA-C22.2 NO. 61010-1.



## MODEL NUMBER

CT3151xx - #

DIM. "A":

'blank' - 12.5 mm (0.492") HORZ

SP - 7.6 mm (0.300") HORZ


V1 - 19.0 mm (0.750") VERT

COLOR: 0 - BLACK  
1 - BROWN  
2 - RED  
4 - YELLOW  
5 - GREEN  
6 - BLUE  
7 - VIOLET (PURPLE)  
8 - GREY  
9 - WHITE

## REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
-	CLASS A RELEASED	10/13/2003	
A	ADDED DIM. "A" AND TABLE TO MODEL NUMBER.	6/20/2006	
B	NOTE 2., ADDED ALT. MATL. 2; NOTE 3, WAS IEC61010-031; ADDED NOTES 6 & 7.	12/20/2007	
C	NOTE 2., DELETED ALT. 1 & 2 (PP); NOTE 3., WAS UL61010B-1; DELETED NOTE 6.	1/25/2008	
D	ADDED SHEET 2 W/LINE DRAWING; NOTE 2., REVISED INSULATOR MATERIAL, WAS A221.	6/27/2008	
E	P1, ADDED UL NOTATION, NOTE 6; P2 ADDED CONCENTRICITY NOTATION TO DIAGRAM.	5/22/2009	
F	P1, UPDATED UL INFORMATION; ADDED NOTE 8.	5/28/2012	
G	P1, NOTE 2, ADDED SOLVAY / TO MFG'ER NAME.	2/21/2017	
H	UPDATED DRAWING TO METRIC DIMENSIONING; ADDED SHEET 3, VERTICAL JACK; REVISED SHEET 1 NOTES AND PART NUMBER TABLE; SHEET 2, DIM. 4.8 (.19) WAS 6.4 (.25).	8/9/2017	
J	SHEET 1, NOTE 2, UPDATED INSULATOR MATERIAL, WAS SOLVAY ENGINEERING PLASTICS, A205F.	4/26/2021	B. HANSEN
K	DWG. NO. WAS P315100, DATED 10/13/03, UPDATED TO NEW SW FORMAT; SHEET 1, NOTE 2, ADDED ALTERNATIVE RESIN, TEKNOR APEX CHEMLON 104 H; NOTE 3, +65°C WAS +80°C; SHEETS 2 & 3, ADDED TOLERANCE TO Ø4.0 JACK; DIM. 3.2 WAS 3.0.; DIM. Ø13.4 WAS Ø13.5.	11/17/2021	B. HANSEN

## THIRD ANGLE PROJECTION



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS  
TOLERANCES ARE:

X.X = ±0.5 X.X\* = ±0.5\*  
X.XX = ±0.25  
X.XXX = ±0.125

DO NOT SCALE DRAWING

MATERIAL

SEE NOTES

REFERENCE

TREATMENT  
N/A

FINISH

SEE NOTES

PROJECT NO.

N/A

APPROVALS

DATE

DRAWN

WDH

11/17/2021

CHECKER

G. GORGONIO

11/18/2021

ENGR.

B. HANSEN

11/17/2021

DESIGN ACTIVITY

METRIC



22820 Savi Ranch Pkwy.  
Yorba Linda, CA 92887  
USA

TITLE

4mm SHEATHED (SAFETY) JACK,  
HORIZONTAL & VERTICAL PCB MOUNT

SIZE

A

CAGE CODE

43F45

DWG. NO.

CT3151

REV.


K

SCALE


2:1

SHEET

1 OF 3



METRIC	APPROVALS		DATE	SIZE	CAGE CODE	DWG. NO.	REV.
	DRAWN	WDH	11/17/2021	A	43F45	CT3151	K
	CHECKER	G. GORGONIO	11/18/2021	SCALE	1:1	SHEET	2 OF 3



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3151-5](#) [CT3151-4](#) [CT3151-2](#) [CT3151-0](#) [CT3151-9](#) [CT3151-6](#) [CT3151-7](#)