

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/11/99	
A	REVISED TO METRIC FORMAT; ADDED NOTES 6 & 7; DIM. 14 (.55)	2/27/18	

1. 4mm INSULATED JACK, THRU-HOLE.

2. SPECIFICATIONS:
INSULATORS: POLYAMIDE (NYLON)
JACK BODY: BRASS, NICKEL PLATED
NUT: BRASS, NICKEL PLATED

3. RATING:
VOLTAGE:
IEC 61010-1: 30 VDC/60 VAC
NON-HANDHELD: 1,200V AC/DC
CURRENT: 36A MAX.
TEMPERATURE: -20° C TO +80° C.

4. MOUNTING HOLE: REFERENCE DIAGRAM.

5. MAXIMUM PANEL THICKNESS: 5 mm (.20)


6. SUPPLIED WITH 1 M6x0.75 HEX NUT

7. RoHS 2 COMPLIANT
EXCEPTION: ANNEX III, 6(c)


PART NUMBER

CT2230-#

COLOR: 0 — BLACK
2 — RED
4 — YELLOW
5 — GREEN
6 — BLUE
9 — WHITE



4. MOUNTING HOLE

METRIC	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLE .X ± 0.8 ± 2° .XX ± 0.25 DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610					
		APPROVALS	DATE	TITLE					
THIRD ANGLE PROJECTION	MATERIAL	DRAWN	WDH	7/11/99		4 mm INSULATED JACK, THRU-HOLE			
	CHECKED					SIZE	CAGE CODE	DWG. NO.	REV.
	FINISH	ENGR.				A	43F45	P223000	A
		DESIGN ACTIVITY							
						SCALE	1:1	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2230-0](#) [CT2230-4](#) [CT2230-6](#) [CT2230-9](#) [CT2230-5](#) [CT2230-2](#)