


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:
JACKET: SILICONE. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR" OD: 3.7 ± 0.2 (.146 \pm .008)
CONDUCTOR: BARE COPPER, STRANDING 195 x 0.07 mm = 0.75 mm², 18 AWG.
- RATING:
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031
CURRENT: 12 A MAX.
TEMPERATURE: -60° C TO +180° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.
- RoHS2 COMPLIANT.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED (REF. DWG. P279900)	7/22/2020	



MODEL NUMBER

CT2799A-#-XXX

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

LENGTH: 10 - 10 m PACKAGE
50 - 50 m SPOOL
100 - 100 m SPOOL

METRIC	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLE .X \pm 0.8 \pm 2° .XX \pm 0.25		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
	DO NOT SCALE DRAWING		APPROVALS DATE					
THIRD ANGLE PROJECTION	MATERIAL		DRAWN WDH		7/22/2020		TITLE	
	FINISH		CHECKED				WIRE, TEST LEAD, SILICONE JACKET, 0.75 mm ² , 18 AWG, 12 A	
			ENGR.				SIZE	REV.
			DESIGN ACTIVITY				A	—
					CAGE CODE		DWG. NO.	
					43F45		P2799A0	
					SCALE		SHEET	
					NONE		1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2799A-4-10](#) [CT2799A-4-100](#) [CT2799A-4-50](#) [CT2799A-5-10](#) [CT2799A-5-100](#) [CT2799A-5-50](#) [CT2799A-6-10](#)
[CT2799A-6-100](#) [CT2799A-6-50](#) [CT2799A-9-10](#) [CT2799A-9-100](#) [CT2799A-9-50](#)