


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:  
JACKET: PVC. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR"  
OD: .150±.008 (3.8 mm)  
CONDUCTOR: BARE COPPER, STRANDING 259 x 0.07 mm = 1.00 mm<sup>2</sup>, 17 AWG.
- RATING:  
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031  
CURRENT: 20 A MAX.  
TEMPERATURE: -20° C TO +80° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS – SEE MODEL NUMBER BELOW.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
–	CLASS A RELEASED	7/11/99	
A	UPDATED FORMAT w/ CAGE CODE	4/18/04	



**MODEL NUMBER**

**CT2880-#-XXX**

COLOR: 0 – BLACK  
2 – RED  
4 – YELLOW  
5 – GREEN  
6 – BLUE  
9 – WHITE

LENGTH: 10 – 10 m PACKAGE  
50 – 50 m SPOOL  
100 – 100 m SPOOL

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		<b>Cal Test Electronics</b> 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610					
		MATERIAL		APPROVALS		DATE		TITLE <b>WIRE, TEST LEAD, PVC JACKET, 1.00 mm<sup>2</sup>, 17 AWG, 20 A</b>			
				DRAWN WDH		7/11/99					
				CHECKED							
		FINISH		ENGR.				SIZE	CAGE CODE	DWG. NO.	REV.
NEXT ASSY				DESIGN ACTIVITY				<b>A</b>	<b>43F45</b>	<b>P288000</b>	<b>A</b>
APPLICATION								SCALE	<b>NONE</b>	SHEET	<b>1 OF 1</b>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Cal Test Electronics:

[CT2880-6-10](#) [CT2880-2-100](#) [CT2880-0-100](#) [CT2880-4-10](#) [CT2880-0-10](#) [CT2880-4-50](#) [CT2880-6-100](#) [CT2880-6-50](#) [CT2880-0-50](#) [CT2880-2-10](#) [CT2880-5-100](#) [CT2880-5-50](#) [CT2880-5-10](#) [CT2880-9-50](#) [CT2880-4-100](#) [CT2880-9-10](#) [CT2880-9-100](#) [CT2880-2-50](#)