




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

RPC-3.50 side

According to

Mechanically compatible with

IEC 60169-23

RPC-2.92 and SMA

SMB Fakra side

According to

DIN 72594-1

Documents

Application note

AN001 "Calibration Services"

Material and plating

Connector parts

Center conductor

Outer conductor RPC-3.50

Outer conductor SMB Fakra

Dielectric RPC-3.50

Dielectric SMB Fakra

Locking ring SMB Fakra

Housing SMB Fakra

Secondary Lock SMB Fakra

Material

CuBe

Stainless steel

Brass

PS

PTFE

CuBe

PBT-GF20

PBT-GF10

Plating

Gold, min. 1.27 µm, over nickel

Passivated

AuroDur®, gold plated

Electrical data

Frequency	DC to 6 GHz
Return loss	≥ 35 dB, DC to 1 GHz
	≥ 26 dB, 1 GHz to 3 GHz
	≥ 21 dB, 3 GHz to 6 GHz

Mechanical data

	RPC-3.50	SMB Fakra
Mating cycles	≥ 500	≥ 500 (SMB Fakra Interface)
		≥ 25 (SMB Fakra housing)
Maximum torque	1.70 Nm	
Recommended torque	0.90 Nm	
Engagement force		≤ 25 N
Disengagement force		≥ 2 N
Gauge	0.00 mm to 0.08 mm	

General standard definition

For proper operation the vector network analyzer (VNA) needs a model describing the electrical behaviour of this calibration standard. The different models, units, and terms used will depend on the VNA type and they will have to be entered into the VNA. All values are based on typical geometry and plating.

Offset Z_0 / Impedance / Z_0	50 Ω
Offset Delay	157.3250 ps
Length (electrical) / Offset Length	47.16 mm
Offset Loss	2.07 G Ω /s
Loss	0.0283 dB/ $\sqrt{\text{GHz}}$

Environmental data

Operating temperature range ¹	+20 °C to +26 °C
Rated temperature range of use ²	0 °C to +50 °C
Storage temperature range	- 40 °C to +85 °C

RoHS	compliant
------	-----------

¹ Temperature range over which these specification are valid.

² This range is underneath and above the operating temperature range, within the calibration adaptor is fully functional and could be used without damage.

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet				Rosenberger									
Calibration Adaptor RPC-3.50 Jack – SMB Fakra Jack				03K159-K20S3									
Declaration of calibration options Factory Calibration Standard delivery for this calibration standard includes a Factory Calibration. The Calibration Certificate issued reports individual calibration results, traceable to Rosenberger standards, national / international standards are not available. Model based standard definitions are reported in an Agilent/Keysight, Rohde & Schwarz and Anritsu compatible VNA format. Accredited Calibration Not available. For further, more detailed information see application note AN001 on the Rosenberger homepage. Calibration interval <table><tr><td>Recommendation</td><td>12 months</td></tr></table> Packing <table><tr><td>Standard</td><td>1 pce in box</td></tr><tr><td>Weight</td><td>10.7 g/pce</td></tr></table>								Recommendation	12 months	Standard	1 pce in box	Weight	10.7 g/pce
Recommendation	12 months												
Standard	1 pce in box												
Weight	10.7 g/pce												
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.													
Draft		Date		Rev.		Engineering change number							
Approved		Date		Name		Date							
Herbert Babinger		07.10.04		S. Andorfer		23.01.18							
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 3 / 3						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[03K159-K20S3](#)