



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to IEC 61169-23
Mechanically compatible with RPC-2.92 and SMA

Contents and Documentation

- This kit is delivered with
- **Standard Definitions Card**
Printed Standard Definitions that can be used on nearly all Vector Network Analyzers
 - **Test Results Documentation**
 - **Hard Shell Case**
 - **Protection Caps**

Material and plating

Connector parts

Center conductor
Outer conductor
Body
Dielectric
Substrate

Material

CuBe
Stainless steel
Aluminum
PS
Al₂O₃

Plating

Gold, min. 1.27 µm, over nickel
Passivated
black anodized

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09_14/6.2

Electrical data

Fr Frequency range	DC to 26.5 GHz
Thru	
Return loss	≥ 34 dB, DC to 4 GHz ≥ 32 dB, 4 GHz to 8 GHz ≥ 30 dB, 8 GHz to 26.5 GHz
Open	
Error from nominal phase ¹	≤ 1.0°, DC to 4 GHz ≤ 2.0°, 4 GHz to 8 GHz ≤ 3.0°, 8 GHz to 26.5 GHz
Short	
Error from nominal phase ²	≤ 1.0°, DC to 4 GHz ≤ 2.0°, 4 GHz to 8 GHz ≤ 3.0°, 8 GHz to 26.5 GHz
Load	
Return loss	≥ 40.0 dB, DC to 4 GHz ≥ 35.0 dB, 4 GHz to 8 GHz ≥ 30.0 dB, 8 GHz to 26.5 GHz
DC Resistance	50 Ω ± 0.5 Ω
Power handling (at 25 °C, sea level)	≤ 0.5 W, derate by 0.005 W/K

¹ The nominal phase is defined by the Offset Delay, the Offset Loss and the Fringing Capacitances

² The nominal phase is defined by the Offset Delay, the Offset Loss and the Short Inductance

Mechanical data

Mating cycles	≥ 500
Maximum torque	1.70 Nm
Recommended torque	0.90 Nm
Gauge	0.00 mm to 0.08 mm

General standard definitions

For proper operation the vector network analyzer (VNA) needs a model describing the electrical behaviour of this calibration standard. The different models, units, and terms used will depend on the VNA type and they will have to be entered into the VNA. All values are based on typical geometry and plating.

Thru

Offset Z ₀ / Impedance / Z ₀	50 Ω
Offset Delay	84.058 ps
Length (electrical) / Offset Length	25.20 mm
Offset Loss	2.51 GΩ/s
Loss	0.0183 dB/√GHz
Line Loss @ 1GHz	0.0007 dB/mm

Open

Offset Z ₀ / Impedance / Z ₀	50 Ω
Offset Delay	33.356 ps
Length (electrical) / Offset Length	10.00 mm
Offset Loss	2.20 GΩ/s
Loss	0.0127 dB/√GHz
Fringing Capacitances	C ₀ = -17.500 x 10 ⁻¹⁵ F / -17.500 fF
	C ₁ = -2000.0 x 10 ⁻²⁷ F/Hz / -2.0000 fF /GHz
	C ₂ = 140.00 x 10 ⁻³⁶ F/Hz / 0.1400 fF /GHz ²
	C ₃ = -2.7000 x 10 ⁻⁴⁵ F/Hz / -0.0027 fF /GHz ³

Short

Offset Z_0 / Impedance / Z_0	50 Ω		
Offset Delay	33.356 ps		
Length (electrical) / Offset Length	10.00 mm		
Offset Loss	2.36 G Ω /s		
Loss	0.0137 dB/ $\sqrt{\text{GHz}}$		
Short Inductance	$L_0 = -44.000 \times 10^{-12} \text{ H}$	/	-44.000 pH
	$L_1 = 3700.0 \times 10^{-24} \text{ H/Hz}$	/	3.7000 pH /GHz
	$L_2 = -250.00 \times 10^{-33} \text{ H/Hz}^2$	/	-0.2500 pH /GHz ²
	$L_3 = 5.0000 \times 10^{-42} \text{ H/Hz}^3$	/	0.0050 pH /GHz ³

Load

Offset Z_0 / Impedance / Z_0	50 Ω
Offset Delay	0.0000 ps
Length (electrical) / Offset Length	0.000 mm
Offset Loss	0.00 G Ω /s
Loss	0.0000 dB/ $\sqrt{\text{GHz}}$

Environmental data

Operating temperature range ³	+20 °C to +26 °C
Rated temperature range of use ⁴	0 °C to +50 °C
Storage temperature range	-40 °C to +85 °C
RoHS	compliant

³ Temperature range over which these specifications are valid.

⁴ This range is underneath and above the operating temperature range, within the calibration kit is fully functional and could be used without damage

Declaration of documentation

Standard delivery for this kit includes Test Results. The documentation issued reports which quantities were tested individually, traceable to national / international standards. Model based standard definitions of the calibration standards are reported in Agilent / Keysight, Rohde & Schwarz and Anritsu compatible VNA format.

Inspection interval

Recommendation	12 months
----------------	-----------

Packing

Standard	1 pce in bag
Weight	34.9 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Marcel Panicke	07.01.16	Markus Müller	29.04.20	f00	19-2083	Marion Striegler	29.04.20

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 3 / 3
--	--	--	--	---	--	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[03K30R-MSOTS3](#)