




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
Mechanically compatible with

IEC 61169-40
RPC-1.85

Documents

Assembly instruction

02 A3

Material and plating

Connector parts

Center contact
Outer contact
Dielectric
Solder sleeve

Material

CuBe
Stainless steel
PEEK
Brass

Plating

Gold, min. 1.27 µm, over chemical nickel
Passivated
Gold, 0.1 µm min.

Technical Data Sheet				Rosenberger			
RPC-2.40		Straight jack		09K121-271S3			
Electrical data Impedance Frequency Return loss Insertion loss Insulation resistance Test voltage (at sea level) Working voltage (at sea level) RF-leakage 50 Ω DC to 50 GHz ≥ 23 dB, DC to 50 GHz ≤ 0.05 x √f(GHz) dB ≥ 5 GΩ 500 V rms 150 V rms ≥ 100 dB up to 1 GHz - Limitations are possible due to the used cable type - Mechanical data Mating cycles Center contact captivation Coupling test torque Recommended torque ≥ 500 ≥ 20 N 1.65 Nm 0.80 Nm to 1.10 Nm Environmental data Temperature range Thermal shock Corrosion Vibration Shock Moisture resistance RoHS -40°C to +85°C IEC 61169-1, Subclause 9.4.4 IEC 61169-1, Subclause 9.4.6 IEC 61169-1, Subclause 9.3.3 IEC 61169-1, Subclause 9.3.14 IEC 61169-1, Subclause 9.4.3 compliant Tooling N/A Suitable cables UT 85, RG 405 /U, RTK-FS 085 Weight 10.0 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	26.08.04	F. Reiner	20.06.18	c01	18-1026	M.Ruf	20.06.18
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[09K121-271S3](#)