



All dimensions are in mm; tolerances according to ISO 2768 m-H

**Interface**

According to

Rosenberger 28K000-000, series QMA  
Rosenberger is an authorised QLF® manufacturer

**Documents**

N/A

**Material and plating**

**Connector parts**

Center contact  
Outer contact  
Body  
Dielectric

**Material**

Beryllium copper  
Brass  
Brass  
PTFE

**Plating**

AuroDur, gold plated  
White bronze(e.g. Optalloy®)  
White bronze(e.g. Optalloy®)

ADAPTOR  
QMA JACK -JACK**28K101-K00N5****Electrical data**

Impedance	50 $\Omega$
Frequency	DC to 18 GHz
Return loss	$\geq 32$ dB, DC to 3 GHz $\geq 28$ dB, 3 to 6 GHz
Insertion loss	$\leq 0.05 \times \sqrt{f(\text{GHz})}$ dB, DC to 6 GHz
Insulation resistance	$\geq 5 \times 10^3$ M $\Omega$
Center contact resistance	$\leq 3$ m $\Omega$
Outer contact resistance	$\leq 2.5$ m $\Omega$
Test voltage, at sea level, 50Hz	1000 V rms
Working voltage, at sea level, 50Hz	480 V rms
RF-leakage	$\geq 95$ dB up to 2 GHz $\geq 80$ dB up to 4 GHz $\geq 70$ dB up to 6 GHz
Intermodulation (3 <sup>rd</sup> order)	$\leq -120$ dBc @ 2 x 20 W

**Mechanical data**

Mating cycles	min. 100
Center contact captivation: axial	$\geq 20$ N
Engagement force	typ. 25 N
Disengagement force	typ. 20 N
Retention force for interface	60 N min.

**Environmental data**

Temperature range	-40°C to +85°C
Storage temperature	-40°C to +85°C
Thermal shock	IEC 60169-1 16.4 (-40 / +85°C)
Corrosion	IEC 60169-1 16.7 (48 hrs)
Vibration	IEC 60068-2-64 random
Damp heat, steady state	IEC 60169-1 16.3 (96 hrs)
RoHS	compliant

**Tooling**

N/A

**Suitable cables**

N/A

**Weight**

Weight 3.2 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Inge Mühlauer	05/10/04	Sa. Krautenbacher	13.03.14	d00	14-0352	T. Krojer	13.03.14
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany <a href="http://www.rosenberger.de">www.rosenberger.de</a>					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: <a href="mailto:info@rosenberger.de">info@rosenberger.de</a>		Page 2 / 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[28K101-K00N5](#)