


Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/08.13/6.1

Technical Data Sheet		Rosenberger
TNC 50 Ω	ADAPTOR JACK - JACK	56K501-K00N5
		
All dimensions are in mm; tolerances according to ISO 2768 m-H		
Interface		
According to		IEC 60169-17, MIL-PRF-39012, DIN EN 122200
Documents		
Panel piercing		B 3
Material and plating		
Connector parts		Material
Center contact		CuBe
Outer contact		Brass
Body		Brass
Dielectric		PTFE
Gasket		NBR
		Plating
		AuroDur®, gold plated
		Flash white bronze over silver(e.g. Optargen®)
		Flash white bronze over silver(e.g. Optargen®)
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de		Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de
		Page 1 / 2

Technical Data Sheet				Rosenberger			
TNC 50 Ω		ADAPTOR JACK - JACK		56K501-K00N5			
Electrical data Impedance50 Ω FrequencyDC to 10 GHz Return loss≥ 30 dB @ DC to 2.5 GHz ≥ 20 dB @ 2.5 GHz to 6 GHz Insertion loss≤ 0.05 x √ f [GHz] dB, DC to 6 GHz Insulation resistance≥ 5 GΩ Center contact resistance≤ 1.5 mΩ Outer contact resistance≤ 1 mΩ Test voltage (at sea level)1500 V rms Working voltage (at sea level)500 V rms Power handling (at 20 °C, sea level, VSWR 1.0)80 W @ 2 GHz							
Mechanical data Mating cycles≥ 500 Center contact captivation: axial≥ 15 N Coupling test torque≤ 1.7 Nm Recommended torque0.46 Nm to 0.69 Nm							
Environmental data Temperature range-25 °C to +110 °C Thermal shockMIL-STD-202, Method 107, Condition B CorrosionMIL-STD-202, Method 101, Condition B VibrationMIL-STD-202, Method 204, Condition B ShockMIL-STD-202, Method 213, Condition G Moisture resistanceMIL-STD-202, Method 106 Degree of protection (mated pair)IEC 60529, IP 68 (assembled in housing) RoHScompliant							
Tooling N/A							
Suitable cables N/A							
Weight Weight22.1 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft		Date		Approved		Date	
Inge Mühlauer		10.08.04		Sa. Krautenbacher		19.03.14	
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de			Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[56K501-K00N5](#)