



All dimensions are in mm; tolerances according to ISO 2768 m-H

**Interface**

According to IEC 61169-24<sup>1</sup>, EIA-550

<sup>1</sup> Accepts only limited pin diameter, see "Mechanical data".

**Documents**

Application note AN001 "Calibration Services"

**Material and plating**

**Connector parts**

	Material	Plating
Center contact	CuBe	Gold, min. 1.27 μm, over nickel
Outer contact	Stainless steel	Passivated
Dielectric	PS	

**Electrical data**

Frequency range	DC to 6 GHz
Return loss	≤ 0.10 dB, DC to 4 GHz ≤ 0.15 dB, 4 GHz to 6 GHz
Error from nominal phase <sup>2</sup>	≤ 1.0°, DC to 4 GHz ≤ 1.5°, 4 GHz to 6 GHz

<sup>2</sup> The nominal phase is defined by the Offset Delay, the Offset Loss and the Fringing Capacitances.

**Mechanical data**

Mating cycles	≥ 1000
Maximum torque	6.78 Nm
Recommended torque	2.00 Nm
Permitted male pin diameter <sup>3</sup>	0.76 mm to 0.86 mm
Gauge	0.00 mm to 0.10 mm

<sup>3</sup> Connecting a F plug with larger male pin diameter will damage female contact fingers of this Open circuit. Use "full range adaptor" 74S121-K22S3 instead.

**General standard definitions**

For proper operation the vector network analyzer (VNA) needs a model describing the electrical behaviour of this calibration standard. The different models, units, and terms used will depend on the VNA type and they will have to be entered into the VNA. All values are based on typical geometry and plating.

Offset Z <sub>o</sub> / Impedance / Z <sub>o</sub>	75 Ω
Offset Delay	53.370 ps
Length (electrical) / Offset Length	16.00 mm
Offset Loss	2.40 GΩ/s
Loss	0.0148 dB/√GHz
Fringing Capacitances <sup>4</sup>	

<sup>4</sup> Fringing Capacitances are determined individually for each Open circuit and are documented in a Calibration Certificate.

**Environmental data**

Operating temperature range <sup>5</sup>	+20 °C to +26 °C
Rated temperature range of use <sup>6</sup>	0 °C to +50 °C
Storage temperature range	- 40 °C to +85 °C

RoHS compliant

<sup>5</sup> Temperature range over which these specification are valid.

<sup>6</sup> This range is underneath and above the operating temperature range, within the open circuit is fully functional and could be used without damage.

# Technical Data Sheet

# Rosenberger

F 75  $\Omega$

Open Circuit  
Jack

74K12L-001S3

## Declaration of calibration options

### Factory Calibration

Standard delivery for this calibration standard includes a Factory Calibration. The Calibration Certificate issued reports individual calibration results, **traceable to Rosenberger standards**, national / international standards are not available. Model based standard definitions are individually optimized and reported in an Agilent/Keysight, Rohde & Schwarz and Anritsu compatible VNA format.

### Accredited Calibration

Not available.

*For further, more detailed information see application note AN001 on the Rosenberger homepage.*

## Calibration interval

Recommendation 12 months

## Packing

Standard 1 pce in box  
Weight 28.5 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Marcel Panicke	08.08.18	Markus Müller	09.05.19	b00	19-0897	Marion Striegler	09.05.19

  

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de	Tel. : +49 8684 18-0 Email : info@rosenberger.de	Page 3 / 3
--	---	---------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[74K12L-001S3](#)