


Technical Data Sheet

Rosenberger

Cable assembly

RPC-1.00 Plug – RTK 047-F – RPC-1.00 Plug

L70-334-XXX



All dimensions are in mm; tolerances: ± 3 mm for $A \leq 300$ mm; $\pm 1\%$ for $A > 300$ mm

*) If length "A" ≤ 90 mm marking is mount centric ± 5 mm

Available variants

Type	max. Insertion loss	Marking	Weight (g) / pce
L70-334-XXX	$\leq 0.0020 * \sqrt{f[\text{GHz}]} + 0.00008 * f[\text{GHz}] \frac{\text{dB}}{\text{mm}}$	ROSENBERGER L70-334-XXX YYYY-WW sssss	$0.0056 \frac{\text{g}}{\text{mm}} * A[\text{mm}] + 3.40\text{g}$

XXX – length in mm = A Maximum possible length = 6000mm

WW – week YYYY – year sssss – serial no.

Note: Weight:

First constant = Cable weight per mm; Second Constant = Connector left and Connector right weight per pce

Assembly parts

Connector left	RPC-1.00 Plug
Connector right	RPC-1.00 Plug
Cable	RTK 047-F
Armour	none

Electrical data

Impedance	50 Ω
Frequency	DC to 110 GHz
Return loss ¹	≥ 12 dB, DC to 50 GHz ≥ 10 dB, 50 to 110 GHz
Insertion loss ¹	see table available variants

¹ Return Loss and Insertion Loss includes the measurement adaptor

Mechanical data

Minimum bend radius static	7.0 mm
Minimum bend radius dynamic	14.0 mm

Environmental data

Temperature range	- 40 °C to +125 °C
RoHS	compliant

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Marcel Panicke	20.09.19	Ronny Mark	11.12.19	a00	19-s271	Marcel Panicke	11.12.19

Rosenberger Hochfrequenztechnik GmbH & Co. KG
P.O.Box 1260 D-84526 Tittmoning Germany
www.rosenberger.de

Tel. : +49 8684 18-0
Email : info@rosenberger.de

Page

1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[L70-334-140](#)