


RPC-N
75 Ω

Open Circuit
Jack

P5K12L-00AS3



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to IEC 61169-16

Documents

Application note AN001 "Calibration Services"

Material and plating

Connector parts

Center conductor
Outer conductor
Dielectric

Material

CuBe
Stainless steel
PS

Plating

Gold, min. 1.27 μm , over nickel
Passivated

Electrical data

Frequency range	DC to 12 GHz
Return loss	≤ 0.10 dB, DC to 4 GHz ≤ 0.15 dB, 4 GHz to 8 GHz ≤ 0.20 dB, 8 GHz to 12 GHz
Error from nominal phase ¹	$\leq 1.5^\circ$, DC to 4 GHz $\leq 3.0^\circ$, 4 GHz to 8 GHz $\leq 4.0^\circ$, 8 GHz to 12 GHz

¹ The nominal phase is defined by the Offset Delay, the Offset Loss and the Fringing Capacitances.

Mechanical data

Mating cycles	≥ 500
Maximum torque	1.70 Nm
Recommended torque	1.10 Nm
Gauge	5.18 mm to 5.26 mm

General standard definitions

For proper operation the vector network analyzer (VNA) needs a model describing the electrical behaviour of this calibration standard. The different models, units, and terms used will depend on the VNA type and they will have to be entered into the VNA. All values are based on typical geometry and plating.

Offset Z_0 / Impedance / Z_0	75 Ω
Offset Delay	41.095 ps
Length (electrical) / Offset Length	12.32 mm
Offset Loss	1.20 G Ω /s
Loss	0.0057 dB/ $\sqrt{\text{GHz}}$
Fringing Capacitances ²	

² Fringing Capacitances are determined individually for each open circuit and are documented in a Calibration Certificate.

Environmental data

Operating temperature range ³	+20 $^\circ\text{C}$ to +26 $^\circ\text{C}$
Rated temperature range of use ⁴	0 $^\circ\text{C}$ to +50 $^\circ\text{C}$
Storage temperature range	-40 $^\circ\text{C}$ to +85 $^\circ\text{C}$

RoHS	compliant
------	-----------

³ Temperature range over which these specification are valid.

⁴ This range is underneath and above the operating temperature range, within the calibration adaptor is fully functional and could be used without damage.

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet				Rosenberger									
RPC-N 75 Ω		Open Circuit Jack		P5K12L-00AS3									
<div>Declaration of calibration options</div> <div>Factory Calibration</div> <p>Standard delivery for this calibration standard includes a Factory Calibration. The Calibration Certificate issued reports individual calibration results, traceable to national / international standards. Model based standard definitions are individually optimized and reported in an Agilent/Keysight, Rohde & Schwarz and Anritsu compatible VNA format.</p> <div>Accredited Calibration</div> <p>Optional this calibration standard can be delivered with an Accredited Calibration (DAkkS) having the highest confidence in the traceability. The DAkkS Calibration Certificate issued reports individual calibration results in a complex format, traceable to national / international standards. Model based standard definitions are individually optimized and reported in an Agilent/Keysight, Rohde & Schwarz and Anritsu compatible VNA format as well as in a dense data set needed for data based standard definitions. The uncertainties are smaller than in a Factory Calibration.</p> <p>For further, more detailed information see application note AN001 on the Rosenberger homepage.</p> <div>Calibration interval</div> <table><tr><td>Recommendation</td><td>12 months</td></tr></table> <div>Packing</div> <table><tr><td>Standard</td><td>1 pce in box</td></tr><tr><td>Weight</td><td>52.0 g/pce</td></tr></table>								Recommendation	12 months	Standard	1 pce in box	Weight	52.0 g/pce
Recommendation	12 months												
Standard	1 pce in box												
Weight	52.0 g/pce												
<p>While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.</p>													
Draft		Date		Rev.		Engineering change number							
Marion Striegler		27.02.14		f00		16-1267							
Approved		Date		Name		Date							
Markus Müller		10.08.16		Marion Striegler		10.08.16							
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 3 / 3						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[P5K12L-00AS3](#)