



Contents

Device	Part number	Quantity
Cable assembly RPC-3.50 jack / RPC-3.50 plug	LU7-055-600	2

Documents

Technical data sheet cable assembly:
RPC-3.50 jack / RPC-3.50 plug

LU7-055-XXX

Electrical data

Impedance	50 Ω
Frequency	DC to 26.5 GHz
Return loss	≥ 26 dB, DC to 4 GHz ≥ 20 dB, 4 GHz to 26.5 GHz
Insertion loss	≤ 1.62 dB at 26.5 GHz
Phase deviation: After 90° bending	≤ 1.0°, DC to 4 GHz ≤ 3.0°, 4 GHz to 26.5 GHz
Straight after 3x90° bending	≤ 0.5°, DC to 4 GHz ≤ 1.5°, 4 GHz to 26.5 GHz
Amplitude stability	≤ 0.03 dB, DC to 4 GHz ≤ 0.05 dB, 4 GHz to 26.5 GHz
Return loss stability	≥ 48 dB, DC to 4 GHz ≥ 40 dB, 4 GHz to 26.5 GHz
RF-leakage	≥ 100 dB up to 1 GHz

Mechanical data

Minimum bend radius	60 mm
---------------------	-------

Environmental data

Temperature range	-40°C to +85°C
RoHS	compliant

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	03/08/06	Martin Moder	07/08/17	e00	17-1214	M.Ruf	07/08/17
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: info@rosenberger.de		Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[VA26-3.50m-3.50f-60](#)