

CHERRY GENTIX SILENT



Models may vary from the image shown

Quiet, No-Click Designer Mouse for Busy Work Environments

The ideal mouse for quiet work environments due to special no-click buttons, perfect ergonomics and a precise sensor.

Key Benefits

- Special no-click buttons, ideal for offices with open floor plan
- Perfect ergonomics for hands both small and large
- Precise sensor with 1000 dpi resolution
- Pleasant to the touch due to abrasion-proof surface finish
- Rubber-coated side sections for optimal grip
- Extra long USB cable (approx. 6 ft)

Technical Data:

Weight (product):

approx. 116 g / approx. 4.09 oz

Total Weight (with packaging):

approx. 150 g / approx. 5.29 oz

Cable Length:

approx. 1.80 m / approx. 5.91 ft

Storage Temperature:

-20°C to 60°C / -4° F to 140° F

Operating Temperature:

0°C to 40°C / 32° F to 104° F

Current Consumption:

max. 100 mA

Interface:

- USB

Product Approvals:

- CE
- FCC
- cTUVus
- RCM
- TÜV-Rheinland/GS



System Requirements:

- USB connection

Box Contents:

- CHERRY GENTIX SILENT
- Operating instructions in hard copy

Dimensions (product):

approx. 112 x 68 x 35 mm / approx. 4.41 x 2.68 x 1.38 in

Packaging Dimensions:

approx. 138 x 97 x 48 mm / approx. 5.43 x 3.82 x 1.89 in

Reliability:

- Standard keys: >3 mill. operations

Mouse:

- Scanning: Optical
- Resolution: 1000 dpi
- Number of Keys: 3
- Mouse Wheel Design: Scroll wheel with key function
- Design: Symmetrical
- Connection: USB
- Housing Color: black
- Key Color: black

Packaging Unit:

- Number of products in the master package: 40
- Number of master packages per pallet: 21

Warranty:

3-year limited manufacturer's guarantee

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences,

as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery delays may occur.
Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product Name	Order Number	EAN Code
1	CHERRY GENTIX SILENT	JM-0310-2	4025112088322

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CHERRY:](#)

[JM-0310-2](#)