



Grove - Barometer Sensor (BMP180)

Release date : 9/20/2015

Version : 1.0

Wiki: [http://www.seeedstudio.com/wiki/Grove - Barometer Sensor \(BMP180\)](http://www.seeedstudio.com/wiki/Grove_-_Barometer_Sensor_(BMP180))

Bazaar: <http://www.seeedstudio.com/depot/Grove-Barometer-Sensor-BMP180-p-1840.html>

Document Revision History

Revision	Date	Author	Description
1.0	Sep 21, 2015	Victor.He	Create file

Contents

Document Revision History	2
1. Introduction	2
2. Features	3
3. Application Ideas	4
4. Specifications	5
5. Usage	6
5.1 With Arduino	6
5.2 With Raspberry Pi	8
6. Resources	11

Disclaimer

For physical injuries and possessions loss caused by those reasons which are not related to product quality, such as operating without following manual guide, natural disasters or force majeure, we take no responsibility for that.


Under the supervision of Seeed Technology Inc., this manual has been compiled and published which covered the latest product description and specification. The content of this manual is subject to change without notice.

Copyright

The design of this product (including software) and its accessories is under tutelage of laws. Any action to violate relevant right of our product will be penalized through law. Please consciously observe relevant local laws in the use of this product.

1. Introduction

This is a Grove module for the Bosch BMP180 high-precision, low-power digital barometer. The BMP180 offers a pressure measuring range of 300 to 1100 hPa with an accuracy down to 0.02 hPa in advanced resolution mode. It's based on piezo-resistive technology for high accuracy, ruggedness and long term stability. The chip only accepts 1.8V to 3.6V input voltage. However, with outer circuit added, this module becomes compatible with 3.3V and 5V. Therefore, it can be used on Arduino/Seeeduino or Seeeduino Stalker without modification. It is designed to be connected directly to a micro-controller via the I2C bus.



2. Features

- Digital two wire (I2C) interface
- Wide barometric pressure range
- Flexible supply voltage range
- Ultra-low power consumption
- Low noise measurement
- Factory-calibrated
- -40 to +85°C operational range, $\pm 2^\circ\text{C}$ temperature accuracy
- I2C address: 0x77

3. Application Ideas

- Enhancement of GPS navigation
- Indoor and outdoor navigation
- Leisure and sports
- Weather forecast
- Vertical velocity indication (rise/sink speed)

4. Specifications

Item	Min	Typical	Max	Unit
Voltage	3	5	5.5	VDC
Current	1.1	/	20	uA
Pressure Range	300	/	1100	hPa
Faster I2C data transfer	/	/	3.4	MHZ
Dimension	40.1*20.2*9.7			mm

5. Usage

5.1 With [Arduino](#)


Barometric condition is one of the criteria used to predict coming change in weather and deduce altitude above sea level. Here is a demo to show you how to read the barometric data from this Grove - Barometer Sensor (BMP180).

1. Connect it to IIC port of Seeeduino or Grove - Base Shield via a Grove cable. And connect Arduino to PC via a USB cable.
2. Download [the library](#)(the barometer library is shared by Grove - Barometer Sensor (BMP180) and Grove - Barometer Sensor(BMP085));Unzip it into the libraries file of Arduino IDE by the path: ..\arduino-1.0.1\libraries.
3. Create a new Arduino sketch and paste the codes below to it or open the code directly by the path: File -> Example ->Barometer_Sensor->Barometer_Sensor.


```
/* Barometer demo V1.0
 * Based largely on code by Jim Lindblom
 * Get pressure, altitude, and temperature from the BMP085.
 * Serial.print it out at 9600 baud to serial monitor.
 *
 * By:http://www.seeedstudio.com
 */
#include "Barometer.h"
#include <Wire.h>
float temperature;
float pressure;
float atm;
float altitude;
Barometer myBarometer;
void setup(){
  Serial.begin(9600);
  myBarometer.init();
}

void loop()
{
  temperature = myBarometer.bmp085GetTemperature(myBarometer.bmp085ReadUT()); //Get the
temperature, bmp085ReadUT MUST be called first
  pressure = myBarometer.bmp085GetPressure(myBarometer.bmp085ReadUP()); //Get the temperature
altitude = myBarometer.calcAltitude(pressure); //Uncompensated calculation - in Meters
  atm = pressure / 101325;
```

```
Serial.print("Temperature: ");  
Serial.print(temperature, 2); //display 2 decimal places  
Serial.println("deg C");  
  
Serial.print("Pressure: ");  
Serial.print(pressure, 0); //whole number only.  
Serial.println(" Pa");  
  
Serial.print("Ralated Atmosphere: ");  
Serial.println(atm, 4); //display 4 decimal places  
  
Serial.print("Altitude: ");  
Serial.print(altitude, 2); //display 2 decimal places  
Serial.println(" m");  
  
Serial.println();  
  
delay(1000); //wait a second and get values again.  
}
```



Open the serial monitor to receive the sensor's data including temperature, barometric pressure value, relative atmosphere pressure and altitude.



5.2 With Raspberry Pi

1. You should have got a raspberry pi and a grovepi or grovepi+.
2. You should have completed configuring the development environment, otherwise follow [here](#).
3. Connection Plug the sensor to grovepi socket i2c-x(1~3) by using a grove cable.
4. Navigate to the demos' directory:

```
cd yourpath/GrovePi/Software/Python/grove_barometer/adafruit
```

To see the code

```
nano grove_i2c_barometric_sensor_example.py # "Ctrl+x" to exit #
```

```
#!/usr/bin/python

import smbus
import RPi.GPIO as GPIO

#import grovepi
from grove_i2c_barometric_sensor import BMP085
```

```

# =====
# Example Code
# =====

# Initialise the BMP085 and use STANDARD mode (default value)
# bmp = BMP085(0x77, debug=True)
bmp = BMP085(0x77, 1)

# To specify a different operating mode, uncomment one of the following:
# bmp = BMP085(0x77, 0) # ULTRALOWPOWER Mode
# bmp = BMP085(0x77, 1) # STANDARD Mode
# bmp = BMP085(0x77, 2) # HIRES Mode
# bmp = BMP085(0x77, 3) # ULTRAHIRES Mode

rev = GPIO.RPI_REVISION
if rev == 2 or rev == 3:
    bus = smbus.SMBus(1)
else:
    bus = smbus.SMBus(0)

temp = bmp.readTemperature()

# Read the current barometric pressure level
pressure = bmp.readPressure()

# To calculate altitude based on an estimated mean sea level pressure
# (1013.25 hPa) call the function as follows, but this won't be very accurate
# altitude = bmp.readAltitude()

# To specify a more accurate altitude, enter the correct mean sea level
# pressure level. For example, if the current pressure level is 1023.50 hPa
# enter 102350 since we include two decimal places in the integer value
altitude = bmp.readAltitude(101560)

print "Temperature: %.2f C" % temp
print "Pressure:    %.2f hPa" % (pressure / 100.0)
print "Altitude:    %.2f m" % altitude

```

5. Run the demo.

```
sudo python grove_i2c_barometric_sensor_example.py
```

6. Result

```
pi@raspberrypi: ~/software/GrovePi/Software/Python/grove_barometer/adafruit
pi@raspberrypi ~/software/GrovePi/Software/Python/grove_barometer/adafruit $ ls
Adafruit_I2C.py          grove_i2c_barometric_sensor.py
Adafruit_I2C.pyc        grove_i2c_barometric_sensor.pyc
grove_i2c_barometric_sensor_example.py
pi@raspberrypi ~/software/GrovePi/Software/Python/grove_barometer/adafruit $ sudo
python grove_i2c_barometric_sensor_example.py
Temperature: 27.40 C
Pressure: 1006.15 hPa
Altitude: 95.96 m
pi@raspberrypi ~/software/GrovePi/Software/Python/grove_barometer/adafruit $
```

6. Resources

[Grove - Barometer Sensor\(BMP180\) Eagle File](#)

[Barometer Sensor Library](#)

[BMP180 datasheet](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Seeed Studio:](#)

[101020072](#)